

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [1301440053](#)  
**Status:** **Active**  
**Overview:** [Heavy-Duty Industrial Wiring Devices](#)  
**Description:** Safeway Plug, 2 Pole/3 Wire, NEMA 5-20, 125V

**Documents:**

|                                |  |
|--------------------------------|--|
| <a href="#">3D Model</a>       | <a href="#">Brochure (PDF)</a>                       |
| <a href="#">Drawing (PDF)</a>  | <a href="#">RoHS Certificate of Compliance (PDF)</a> |
| <a href="#">3D Model (PDF)</a> |  |

**Agency Certification**

|     |        |
|-----|--------|
| CSA | LR6837 |
| UL  | E10176 |

**General**

|                    |  |
|--------------------|--|
| Product Family     | Wiring Devices                                       |
| Series             | <a href="#">130144</a>                               |
| IP Rating          | N/A  |
| NEMA Configuration | NEMA 5-20  |
| Overview           | <a href="#">Heavy-Duty Industrial Wiring Devices</a> |
| Product Name       | Safeway  |
| Receptacle Type    | N/A  |
| Specialty          | N/A  |
| Taxonomy           | Wiring Devices                                       |
| Type               | Plug   |
| UPC                | 78678870110  |

**Physical**

|               |               |
|---------------|---------------|
| Flange        | No            |
| Flip Lid      | No            |
| Gender        | Male          |
| Length        | N/A           |
| Locking Blade | No            |
| Net Weight    | 67.131/g      |
| Poles         | 2-pole/3-wire |

**Electrical**


|                               |       |
|-------------------------------|-------|
| Cord Type                     | N/A   |
| Current - Maximum per Contact | 20.0A |
| GFCI                          | No    |
| Lighted Connector             | No    |
| Voltage - Maximum             | 125V  |

**Material Info**

|                    |      |
|--------------------|------|
| Engineering Number | 5366 |
|--------------------|------|

**Reference - Drawing Numbers**

|               |                |
|---------------|----------------|
| Sales Drawing | 1301440053-000 |
|---------------|----------------|



*Series image - Reference only*

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant with Exemption 6(c)**

**REACH SVHC**

Not Reviewed

**Halogen-Free**

**Status**

**Not Reviewed**

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

**China RoHS**

50 Image

Not Relevant

Not Contained

**Search Parts in this Series**

[130144 Series](#)