


## 1-6437133-3 Product Details

 [Live Product Chat](#)


### 1-6437133-3

TE Internal Number: 1-6437133-3

 [Active](#)

### FLEXSTRIP® Jumpers

 [Always EU RoHS/ELV Compliant \(Statement of Compliance\)](#)

#### Product Highlights:

- 1.27 mm Centerline
- Nomex Insulation Material
- Insulation Length = 114.30 mm
- Pin Arrangement (Left) = A
- Pin Arrangement (Right) = A

[View all Features](#)

### Quick Links

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

[Add to My Part List](#)  [Request Sample](#)  [Find Similar Products](#)  [Buy Product](#)

### Documentation & Additional Information

#### Product Drawings:

- [FLEXSTRIP PIN CONFIGURATIONS, GENERIC](#) (PDF, English)

#### Catalog Pages/Data Sheets:

- None Available

#### Product Specifications:

- None Available

#### Application Specifications:

- None Available

#### Instruction Sheets:

- None Available

#### CAD Files:

- None Available

#### Additional Information:

- [Product Line Information](#)

#### Additional Product Images:

- [Product View](#)
- [Product View](#)

#### Related Products:

- [Tooling](#)

[List all Documents](#)

### Product Features (Please use the Product Drawing for all design activity)

#### Product Type Features:

- [Insulation Material](#) = Nomex
- [Number of Conductors](#) = 6

#### Electrical Characteristics:

- Current Rating (Amps.) = 1.6
- Impedance (Ω) = 95
- Voltage Rating (VAC) = 200

#### Body Related Features:

- [Centerline \(mm \[in\]\)](#) = 1.27 [0.050]
- [Insulation Length \(mm \[in\]\)](#) = 114.30 [4.500]

#### Configuration Related Features:

- [Pin Arrangement \(Left\)](#) = A
- [Pin Arrangement \(Right\)](#) = A

#### Industry Standards:

- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Not reviewed for lead free solder process
- RoHS/ELV Compliance History = Always was RoHS compliant

#### Conditions for Usage:

- Operating Temperature (°C [°F]) = -40 - +125 [-40 - +257]

#### Other:

- Brand = Tyco Electronics

[Provide Website Feedback](#) | [Need Help?](#)