

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1727670124](#)
Status: **Active**
Overview: [Mini-Fit Family Power Connectors](#)
Description: Mini-Fit TPA2 Plug Housing, 4.20mm Pitch, Dual Row, UL 94V-2 Glow-Wire Capable, 24 Circuits, Panel Mount

Documents:

| | |
|--|---|
| 3D Model | Packaging Specification 1727670001-PK-000 (PDF) |
| 3D Model (PDF) | Test Summary 2029880001-TS-000 (PDF) |
| Drawing (PDF) | Datasheet (PDF) |
| Application Specification AS-172718-0000-001 (PDF) | RoHS Certificate of Compliance (PDF) |



General

| | |
|----------------|---|
| Product Family | Crimp Housings |
| Series | 172767 |
| Application | Power, Wire-to-Board, Wire-to-Wire |
| Comments | See product specification for current derating information. |
| Overview | Mini-Fit Family Power Connectors |
| Product Name | Mini-Fit TPA2 |
| Taxonomy | Connector Housings |
| UPC | 191128363082 |

Physical

| | |
|-------------------------------|----------------|
| Circuits (maximum) | 24 |
| Color - Resin | Black |
| Gender | Plug |
| Glow-Wire Capable | Yes |
| Lock to Mating Part | Yes |
| Material - Resin | Nylon |
| Net Weight | 7.679/g |
| Number of Rows | 2 |
| Packaging Type | Bag |
| Panel Mount | Yes |
| Pitch - Mating Interface | 4.20mm |
| Pitch - Termination Interface | 4.20mm |
| Polarized to Mating Part | Yes |
| Stackable | No |
| Temperature Range - Operating | -40° to +105°C |

Material Info

Reference - Drawing Numbers

| | |
|---------------------------|--------------------|
| Application Specification | AS-172718-0000-001 |
| Packaging Specification | 1727670001-PK-000 |
| Sales Drawing | SD-172767-0000-000 |
| Test Summary | 2029880001-TS-000 |

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2022)4187-DC (10
June 2022)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[172767](#) Series

Mates With

Mini-Fit TPA2 Receptacle Housing [172708](#) .
Mini-Fit Jr. Receptacle Housing [5557](#)

Use With

Mini-Fit TPA2 Male Terminal [172765](#) ,
[203070](#) . Mini-Fit TPA2 Retainer [172709](#)