

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [1301100060](#)  
**Status:** **Active**  
**Overview:** [Wide-Area Lighting Products](#)  
**Description:** Watertite® Wet Location 2 x 20W LED Magnet Mount Area Light, Cord Type 16/3 SJTOW, Cord Length 3.04m (10.0')

**Documents:**

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)  
[Product Specification PS-130110-001 \(PDF\)](#) [Product Literature \(PDF\)](#)

**Agency Certification**

UL E174254

**General**

Product Family Portable Lighting  
 Series [130110](#)  
 NEMA Configuration NEMA 5-15  
 NEMA Rating NEMA 3  
 Outlet None  
 Overview [Wide-Area Lighting Products](#)  
 Product Literature Order No 987651-2651  
 Product Name Watertite®  
 Type Wide Area Lamps  
 UPC 78172544634  
 Woodhead Yes

**Physical**

Cord Length - Primary 3.04m (10.0')  
 Cord Length - Secondary N/A  
 Depth 207.26mm (8.160")  
 Duty Wet Location  
 Guard Included No  
 Guard Type N/A  
 Height 264.16mm (10.400")  
 Length 228.60mm (9.000")  
 Material - Globe Clear Polycarbonate  
 Material - Guard N/A  
 Mounting Style Magnet  
 Packaging Type Carton  
 Socket Construction N/A

**Electrical**

Bulb Type LED - 5000K  
 Cord Type - Primary 16/3 SJTOW  
 Lamp Type LED  
 Lamp Wattage - Maximum 20W x 2  
 Lumens 2700  
 On/Off Switch No  
 Voltage (Fixture) - Maximum 120VAC 60 HZ

**Material Info**

Engineering Number 8565-LED

**Reference - Drawing Numbers**

Product Specification PS-130110-001  
 Sales Drawing SD-130110-004



*Series image - Reference only*

**EU ELV**

**Not Relevant**

**EU RoHS**

**Not Reviewed**

**REACH SVHC**

Not Reviewed

**Halogen-Free**

**Status**

**Not Reviewed**

**Need more information on product environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
 Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS Not Reviewed

ELV Not Relevant

RoHS Phthalates Not Reviewed

**Search Parts in this Series**

[130110 Series](#)

This document was generated on 06/28/2017

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**