


62802 -2 Product Details

Live Product Chat US Only
8:30am - 5pm ET, Mon - Fri



62802 -2

✓ [Active](#)

Multiple Circuit Housings with Tabs & Receptacles Including FASTIN -FASTON

[Always EU RoHS/ELV Compliant](#) ([Statement of Compliance](#))

Product Highlights:

- ? Receptacle
- ? Tab Fit = 4.75 x 0.81 mm
- ? Wire Range = 0.30 -1.40² [22-16] mm [AWG]
- ? Insulation Diameter = 2.30 -3.30 [.091 -.129] mm [in]
- ? Receptacle Style = Straight

[View all Features](#) | [Find Similar Products](#)

Quick Links

- [Check Pricing & Availability](#)
- [Search for Tooling](#)
- [Product Feature Selector](#)
- [Contact Us About This Product](#)

Documentation & Additional Information

Product Drawings:

- ? [RECEPTACLE, FASTIN- FASTON, .187 SERIES](#) (PDF, English)

Catalog Pages/Data Sheets:

- ? None Available

Product Specifications:

- ? None Available

Application Specifications:

- ? None Available

Instruction Sheets:

- ? None Available

CAD Files: ([CAD Format & Compression Information](#))

- ? [2D Drawing](#) (DXF, Version H)
- ? [3D Model](#) (IGES, Version H)
- ? [3D Model](#) (STEP, Version H)

[List all Documents](#)

Additional Information:

- ? [Product Line Information](#)

Related Products:

- ? [Tooling](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- ? [Product Type](#) = Receptacle
- ? [Tab Fit \(mm \[in\]\)](#) = 4.75 x 0.81 [.187 x .032]
- ? [Insulation Diameter \(mm \[in\]\)](#) = 2.30 -3.30 [.091 -.129]
- ? [Receptacle Style](#) = Straight
- ? [Wire/Cable Type](#) = Regular Wire
- ? [Finish](#) = Tin
- ? [Material](#) = Brass
- ? [Insertion Force](#) = Normal
- ? [Insulation Support](#) = With
- ? [Crimp Type](#) = "F"
- ? FASTON = Yes
- ? For Housing Type = Modular

Body Related Features:

- ? [Wire Range \(mm \[AWG\]\)](#) = 0.30 -1.40² [22-16]
- ? Stock Thickness (mm [in]) = 0.30 [0.012]

Industry Standards:

- ? [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- ? [Lead Free Solder Processes](#) = Not relevant for lead free process
- ? RoHS/ELV Compliance History = Always was RoHS compliant

Packaging Related Features:

- ? [Packaging Method](#) = Strip

Other:

- ? Line = FASTIN -FASTON .187
- ? Brand = AMP