



CP16SH10IP6474BF Product Details

[Share](#) | [Print](#) | [Email](#)


Variable Resistors

Always EU RoHS/ELV Compliant (Statement of Compliance)

Product Highlights:

- Variable Resistor
- Resistor Type = Potentiometer
- Resistance Selection = K Ω
- Resistance = 470K Ω
- Power Rating = .10 W

[View all Features](#)

CP16SH10IP6474BF

(7-1676003-1)

TE Internal Number: 7-1676003-1

Active

[Add to My Part List](#) | [Request Sample](#) | [Find Similar Products](#) | [Buy Product](#)

Quick Links

- ▶ [Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

Documentation & Additional Information

Documents are temporarily unavailable. We are working hard to correct the problem. Please try again later.

Additional Information:

- [Product Line Information](#)

Related Products:

- [Tooling](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- Product Type = Variable Resistor
- Resistor Type = Potentiometer
- Element = Carbon
- Sealed = No

Electrical Characteristics:

- Resistance Selection (Ω) = K
- Resistance (Ω) = 470K
- Power Rating (W) = 0.10
- Tolerance (%) = 20

Termination Features:

- Termination Type = PCB Terminations
- Termination Post Orientation = In Line

Body Features:

- Shaft Style = Serrated, 6 x 45mm
- Package, Component Size = 16mm Sq.

Configuration Features:

- Sections = Single
- Adjustment Location = Side
- Adjustment Style = Spindle With Switch
- Operating Function = Single Turn

Industry Standards:

- RoHS/ELV Compliance = RoHS compliant, ELV compliant
- Lead Free Solder Processes = Wave solder capable to 240°C, Wave solder capable to 260°C, Wave solder capable to 265°C
- RoHS/ELV Compliance History = Always was RoHS compliant

Conditions for Usage:

- Temperature Coefficient (ppm/°C) = 1000

Other:

- Series = CP16
- Brand = Citec
- Comment = Nuts fitted.

Feedback

Corporate Information

- [About TE](#)
- [Investors](#)
- [News Room](#)
- [Supplier Portal](#)
- [Careers](#)
- [Terms & Conditions](#)
- [Privacy Policy](#)
- [AODA Accessibility Policy](#)
- [AODA Multi-Year Accessibility Plan](#)

Quick Links

- [Distributor Inventory](#)
- [Product Cross Reference](#)
- [Documents & Drawings](#)
- [Product Compliance Support Center](#)
- [Site Map](#)

Customer Support

- [Email or Chat With Us](#)
- [Find a Phone Number](#)
- [Knowledge Base](#)
- [Manage Your Account](#)

Keep Me Informed



