


## 1571986 -8 Product Details

### Have a Question?

Chat with a Product Information Specialist



### Rocker/Paddle Switches

[Always EU RoHS/ELV Compliant](#) ( [Statement of Compliance](#) )

#### Product Highlights:

- ? Contact Rating = 5A
- ? Single Pole - Double Throw Configuration (Pole - Throw)
- ? Silver Contact Plating
- ? Gemini A Series
- ? Operating Function = On On

[View all Features](#)

#### Quick Links

- [Check Pricing & Availability](#)
- [Search for Tooling](#)
- [Product Feature Selector](#)
- [Contact Us About This Product](#)

**1571986 -8**  
(A101J1AQ004)

TE Internal Number: 1571986 -8

 [Active](#)

 [Add to My Part List](#)



[Request Sample](#)



[Find Similar Products](#)



[Buy Product](#)

#### Documentation & Additional Information

##### Product Drawings:

- ? [GEMINI A SERIES ROCKER SWITCH SINGLE POLE](#) (PDF, English)

##### Catalog Pages/Data Sheets:

- ? [GEMINI SERIES SWITCHES QUICK REF GUIDE 2 -1773458 -5](#) (PDF, English)

##### Product Specifications:

- ? None Available

##### Application Specifications:

- ? None Available

##### Instruction Sheets:

- ? None Available

##### CAD Files:

- ? None Available

##### Additional Information:

- ? [Product Line Information](#)

##### Related Products:

- ? [Tooling](#)

[List all Documents](#)

#### Product Features (Please use the Product Drawing for all design activity)

##### Product Type Features:

- ? Configuration (Pole - Throw) = Single Pole - Double Throw
- ? Actuator Style = Rocker
- ? Actuator Type = Small
- ? Termination Type = Printed Circuit
- ? Mount = Printed Circuit Board
- ? Mount Angle = Right Angle

##### Mechanical Attachment:

- ? Body Color = Black

##### Electrical Characteristics:

- ? Contact Rating = 5A

##### Body Related Features:

- ? Series = Gemini A
- ? Actuator Color = Black
- ? LED = Without

##### Contact Related Features:

- ? Contact Plating = Silver

##### Housing Related Features:

- ? Process Sealed = No

##### Configuration Related Features:

- ? Operating Function = On On
- ? Indicator/Imprint Legend = None

##### Industry Standards:

- ? [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- ? [Lead Free Solder Processes](#) = Wave solder capable to 240°C, Wave solder capable to 260°C, Wave solder capable to 265°C
- ? RoHS/ELV Compliance History = Always was RoHS compliant

##### Purchasing Information:

- ? Lamp = Without

##### Other:

- ? Brand = Tyco Electronics

#### Corporate Information

- [Who We Are](#)
- [Investors](#)
- [News Room](#)
- [Supplier Portal](#)
- [Careers](#)

#### Quick Links

- [Check Distributor Inventory](#)
- [Cross Reference](#)
- [Find Documents & Drawings](#)
- [Product Compliance Support Center](#)
- [Site Map](#)

#### Customer Support

- [Email or Chat with Us](#)
- [Find a Phone Number](#)
- [Search Knowledge Base](#)
- [Manage Your Account](#)

#### Sign up for our eNewsletter

Enter your email address

#### Follow Us On:



#### Visit Us On:

