


926301-3 Product Details

 [Live Product Chat](#)



926301-3

TE Part Number: 926301-3

 [Active](#)

 [Add to Part List](#)

.250" Centerline, 600 V, 19 - 36 A max

 [Always EU RoHS/ELV Compliant \(Statement of Compliance\)](#)

Product Highlights:

- Housing
- Universal MATE-N-LOK
- Not CompactPCI
- 6.35 mm Centerline, Matrix
- Number of Circuits = 8

[View all Features](#) | [Find Similar Products](#)

Quick Links

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)
- ▶ [Request Samples](#)

NEW!

Documentation & Additional Information

Product Drawings:

- [Universal Mate N Lok 8 polig \(PDF, English\)](#)

Catalog Pages/Data Sheets:

- None Available

Product Specifications:

- None Available

Application Specifications:

- None Available

Instruction Sheets:

- None Available

CAD Files: ([CAD Format & Compression Information](#))

- [2D Drawing](#) (DXF, Version F)
- [3D Model](#) (IGES, Version F)
- [3D Model](#) (STEP, Version F)

[List all Documents](#)

Additional Information:

- [Product Line Information](#)

Related Products:

- [Tooling](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- Product Type = Housing
- Connector Line = Universal MATE-N-LOK
- Number of Circuits = 8
- Mount = Free or Panel
- Color = Brick Red
- Lock Type = Positive Lock

Electrical Characteristics:

- High Current = No
- Current Rating (Amps.) = 19
- Voltage (VAC) = 600

Body Related Features:

- Centerline, Matrix (mm [in]) = 6.35 [.250]
- Housing Type = Plug
- Contact Diameter (mm [in]) = 2.13 [0.084]

Contact Related Features:

- CompactPCI = No
- Contact Layout = In-Line
- Sealable = No

Housing Related Features:

- Housing Material = Polyamide
- Housing Flammability Rating = UL 94V-0

Industry Standards:

- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Not relevant for lead free process
- RoHS/ELV Compliance History = Always was RoHS compliant

Packaging Related Features:

- Packaging Method = One Piece Housing

Other:

- Brand = AMP

 [Provide Website Feedback](#) | [Need Help?](#)