



## 1520231-1 Product Details

[Share](#) | [Print](#) | [Email](#)


1520231-1

TE Internal Number: 1520231-1  
**Active**

### Power Toggle Switches

[Not EU RoHS or ELV Compliant](#)

#### Product Highlights:

- Double Pole - Single Throw Configuration (Pole-Throw)
- Toggle Length = 19.45 mm
- Toggle Style = Baton
- Bushing Length = 5.20 mm
- Termination Type = Screw-In Terminal

[View all Features](#)

[Add to My Part List](#) | 
 [Request Sample](#) | 
 [Find Similar Products](#) | 
 [Buy Product](#)

#### Quick Links

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

### Documentation & Additional Information

#### Product Drawings:

- [DIM'S FOR 20A 250V 3 HOLE MTG. TOOL HANDLE SWITCH](#) (PDF, English)

#### Catalog Pages/Data Sheets:

- None Available

#### Product Specifications:

- None Available

#### Application Specifications:

- None Available

#### Instruction Sheets:

- None Available

#### CAD Files:

- None Available

#### Related Products:

- [Tooling](#)

[List all Documents](#)

### Product Features (Please use the Product Drawing for all design activity)

#### Product Type Features:

- Configuration (Pole-Throw) = Double Pole - Single Throw
- Termination Type = Screw-In Terminal

#### Electrical Characteristics:

- UL/CSA 250V Current Rating (A) = 20
- UL/CSA 125V Horse Power Rating (hp) = 1.50
- UL/CSA 250V Horse Power Rating (hp) = 2.00

#### Body Features:

- Mount Type = Mounting Plate

#### Housing Features:

- Toggle Length (mm [in]) = 19.45 [0.766]
- Toggle Style = Baton

#### Configuration Features:

- Bushing Length (mm [in]) = 5.20 [0.205]

#### Industry Standards:

- [RoHS/ELV Compliance](#) = Not ELV/RoHS compliant
- [Lead Free Solder Processes](#) = Not relevant for lead free process

#### Other:

- Brand = Alcoswitch

#### Corporate Information

[Who We Are](#)  
[Investors](#)  
[News Room](#)  
[Supplier Portal](#)  
[Careers](#)

#### Quick Links

[Check Distributor Inventory](#)  
[Cross Reference](#)  
[Find Documents & Drawings](#)  
[Product Compliance Support Center](#)  
[Site Map](#)

#### Customer Support

[Email or Chat With Us](#)  
[Find a Phone Number](#)  
[Search Knowledge Base](#)  
[Manage your Account](#)

#### Keep Me Informed

Receive TE News, Events & Technology Updates

Enter your email address

