




# HMB1131K01P Product Details

[Share](#) | [Print](#) | [Email](#)


✔ Active

## Military/Aerospace High Performance Relays

HMB1131K01P = M39016/22-007P  
**HMB1131K01P** (1-1617038-5)  
 TE Internal Number: 1-1617038-5

### Product Highlights [View All](#)

- HMB Half-Size Relay Series
- Input Voltage = 26.5 VDC
- Contact - Arrangement = 2 Form C, DPDT, 2 C/O
- Contact - Rated Current = 2 A
- Non Polarized, Monostable Coil - Magnetic System

- [Pricing & Availability](#)
- [Request Sample](#)
- [Add to My Part List](#)
- [Buy Product through Distributor](#)

Feedback

**Documents**

**Features**

**Compliance**

**Please Note:**

Use the Product Drawing for all design activity

Product Type Features	
MOSFET Driver	Without
Mechanical Attachment	
Mounting Options	Panel Mount
Electrical Characteristics	
Input Voltage (VDC)	26.5
Contact - Rated Current (A)	2
Coil Suppression Diode	Without
Coil Polarity Protection Diode	Without
Coil - Resistance (Ω)	700
Coil Power Measurement	Milliwatts
Coil - Rated Power, DC (mW)	1003
Actuating System	DC
Shock	100G's, 6ms
Vibration	30G's, 10 to 3000Hz
Termination Features	
Termination Type	Solder Hook Terminal

Body Features	
Enclosure Type	Hermetically Sealed
Configuration Features	
Contact - Arrangement <sup>?</sup>	2 Form C, DPDT, 2 C/O
Coil - Magnetic System	Non Polarized, Monostable
Transistor Driver	Without
Industry Standards	
Government/Industry Qualification	Yes
Government/Industry Part Number	M39016/22-007P
RoHS/ELV Compliance <sup>?</sup>	Not ELV/RoHS compliant
Lead Free Solder Processes <sup>?</sup>	Not suitable for lead free processing
Approved Standards	M39016 Qualified, P Level
Conditions for Usage	
Temperature Range (°C)	-65 - +125
Other	
Series <sup>?</sup>	HMB Half-Size Relay
Brand	CII

**Related Products**

Not quite the product you're looking for?

[Find Similar Products](#)

[View Part in Product Feature Selector](#)

[Check for Tooling](#)

**Corporate Information**

- [About TE](#)
- [Investors](#)
- [News Room](#)
- [Supplier Portal](#)
- [Careers](#)
- [Terms & Conditions](#)
- [Privacy Policy](#)
- [Global Accessibility Statement](#)

**Quick Links**

- [Distributor Inventory](#)
- [Product Cross Reference](#)
- [Documents & Drawings](#)
- [Product Compliance Support Center](#)
- [Site Map](#)

**Customer Support**

- [Email or Chat With Us](#)
- [Find a Phone Number](#)
- [Knowledge Base](#)
- [Manage Your Account](#)

**Keep Me Informed**

