


Relays, Contactors & Switches > Switches > Pushbutton Switches

AV22 DPM 5A MOVE RING LED YELLOW 12V



Alcoswitch | Alcoswitch AV

TE Part # **AV2220E512Q04**

TE Internal #: **4-2213772-9**

Configuration (Pole-Throw) : **Double Pole - Single Throw**

Number of Actuators : **Single**

Actuator Profile : **Flush**

Bushing Style : **Threaded**

Illuminated : **Yes**

[Similar Products](#)

ORDER SAMPLES

Compatible Parts & Tooling

SHOP OUR DISTRIBUTORS

North America

[See all price breaks](#)

Distributor	1	10,000	Buy
NEWARK ELEMENT14	\$15.960	\$12.190	Visit Site
98 in stock			
DIGI-KEY ELECTRONICS	\$16.800	\$12.837	Visit Site
94 in stock			

We are here to help!

Get in touch with our product experts.

CHAT WITH US

EMAIL US

CALL US

Please give us feedback:
Did you find what you need on this page?

YES

Feedback

DOCUMENTS

FEATURES

PRODUCT COMPLIANCE

Product Drawings **AV22 DPM 5A MOVE RING LED YELLOW 12V**
AV22 DPM 5A MOVE RING LED YELLOW 12V
 English

CAD Files **3D PDF**
3D_CVM_CVM_4-2213772-9_A.pdf 3D
 Customer View Model
ENG_CVM_CVM_4-2213772-9_A.2d_dxf.zip
 English
ENG_CVM_CVM_4-2213772-9_A.3d_igs.zip
 English
ENG_CVM_CVM_4-2213772-9_A.3d_stp.zip
 English

Catalog Pages/Data Sheets **ENG_DS_1-1773878-3_Alcoswitch_AntiVandal_0517.pdf** English

Agency Approvals **UL Report**
ENG_AAD_UL_E46765_20030916__A.pdf
 English

Please review product documents or [contact us](#) for the latest agency approval information. Please Note: Use the Product Drawing for all design activity.



Product Type
Features

Dust Proof : **Yes**
Illuminated : **Yes**
Actuator Style : **Round**
Product Type : **Switch**
Switch Type : **Pushbutton**

Configuration
Features

Configuration (Pole-Throw) :
**Double Pole - Single
Throw**
Number of Actuators : **Single**
Snap Action : **Without**
Support Bracket : **Without**
Tactile : **No**
Operating Function : **Momentary**
Detent Style : **Audible**
ESD Grounding Terminal : **Without**

Electrical
Characteristics

Voltage Rating (VAC): **250**

Body Features

Case Material : **PBT**
Actuator Profile : **Flush**
Bushing Style : **Threaded**

Contact Features

Contact Current Rating (A):
5
Switch Contact Plating Material :
Silver

Termination
Features

Termination Type : **Wire Lugs**

Mechanical
Attachment

Mounting Type : **Panel**
Mounting Angle : **Vertical**

Housing Features

Process Sealed : **Yes**

Dimensions

Bushing Length (in): **22**

Statement of
Compliance

[Statement of Compliance pdf](#)



Pushbutton Switches (705)

ABOUT TE CONNECTIVITY

- [Our Company](#)
- [Events](#)
- [TE News Center](#)
- [Careers](#)
- [Investors](#)
- [Corporate Responsibility](#)
- [Terms and Conditions of Sale](#)

FOR PARTNERS

- [Distributors](#)
- [Suppliers](#)

CUSTOMER SUPPORT

- [Email or Call Us](#)
- [Find Authorized Distributors](#)
- [Shop Online in the TE Store](#)
- [Product FAQs](#)

CALL US

- [United States](#)
- [Germany](#)
- [China \(中文\)](#)
- [Japan \(日本語\)](#)
- [Afghanistan \(EN\)](#)
- [Find Your Country/Region](#)

Need help? ✕

Our team is on stand-by and ready to help with your order.

CHAT NOW >