



7022WDIM Product Details

[Share](#) | [Print](#) | [Email](#)


✔ Active

Time Delay Relays

7022WDIM=RLY,STD,OFF,2P,96V,50S,I,M

7022WDIM (6-1755142-4)

TE Internal Number: 6-1755142-4

Product Highlights [View All](#)

- 7000 Electropneumatic Timing - Industrial Series
- Input Voltage = 96 VDC
- Contact - Arrangement = 2 Form C, DPDT, 2 C/O
- Contact Rating = 10A @ 240 VAC
- Mounting Options = Mounting Bracket

[Pricing & Availability](#)
[Request Sample](#)
[Add to My Part List](#)
[Buy Product through Distributor](#)
[Feedback](#)
[Documents](#)
[Features](#)
[Compliance](#)

Please Note:

Use the Product Drawing for all design activity

Product Type Features

Option	Dust-Tight Gasketing, Tamper-Proof Cap - Transparent
--------	--

Mechanical Attachment

Mounting Options	Mounting Bracket
------------------	------------------

Electrical Characteristics

Input Voltage (VDC)	96
Contact Rating	10A @ 240 VAC

Termination Features

Termination Type	Screw Terminal
------------------	----------------

Dimensions

Approx. Dimensions (L x W x H) (mm [in])	114.80 x 65.30 x 71.90 [4.523 x 2.572 x 2.832]
--	--

Contact Features

Delay Time	5 seconds to 50 seconds
Type of Control	Knob
Repeatability, Max.	± 5%

Configuration Features

Contact - Arrangement ?	2 Form C, DPDT, 2 C/O
Multiple Timing Ranges	Without

Industry Standards

Approved Standards	CE Approved, CSA Certified, UL Listed
RoHS/ELV Compliance ?	Not ELV/RoHS compliant
Lead Free Solder Processes ?	Not relevant for lead free process

Conditions for Usage

Temperature Range (°C)	-30 - +75
------------------------	-----------

Operation/Application

Mode of Operation	Off-Delay
-------------------	-----------

Other

Series	7000 Electropneumatic Timing - Industrial
Brand	Agastat

Related Products

Not quite the product you're looking for?

[Find Similar Products](#)

[View Part in Product Feature Selector](#)

[Check for Tooling](#)

Corporate Information

- [About TE](#)
- [Investors](#)
- [News Room](#)
- [Supplier Portal](#)
- [Careers](#)
- [Terms & Conditions](#)
- [Privacy Policy](#)
- [Global Accessibility Statement](#)

Quick Links

- [Distributor Inventory](#)
- [Product Cross Reference](#)
- [Documents & Drawings](#)
- [Product Compliance Support Center](#)
- [Site Map](#)

Customer Support

- [Email or Chat With Us](#)
- [Find a Phone Number](#)
- [Knowledge Base](#)
- [Manage Your Account](#)

Keep Me Informed

