ASE22S04=DPDT AUTOSLIDE ! PENDING OBSOLESCENCE

Alcoswitch | Alcoswitch ASE/F

TE Part # 1825010-8 TE Internal #: 1825010-8

View on TE.com >



Relays, Contactors & Switches > Switches > Slide Switches



Configuration (Pole-Throw): Double Pole - Double Throw

Mounting Angle: Vertical

Contact Base Material: Copper Alloy

Number of Actuators: Single

Number of Positions: 2

Features

Product Type Features

Switch Style	Auto-Insertable
Terminal Configuration	Standard
Actuator Style	Extended, Top

Configuration Features

Configuration (Pole-Throw)	Double Pole - Double Throw
Number of Actuators	Single
Number of Positions	2

Body Features

Actuator Material	Nylon
Actuator Color	Natural

Contact Features

Contact Base Material	Copper Alloy
Contact Current Rating	.3 A
Switch Contact Plating Material	Silver

Mechanical Attachment

PCB Mount Retention	Without
Mounting Angle	Vertical
Mounting Type	Reverse L Leg Configuration, Surface Mount

TE Part # 1825010-8 TE Internal #: 1825010-8



Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUL 2019 (201) Candidate List Declared Against: JUN 2016 (169)
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Reflow solder capable to 260°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulations, TE's information on SVHC in articles for this part number is still based on the European Chemical Agency (ECHA) 'Guidance on requirements for substances in articles' (Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An Article Always An Article) stating that, in case of 'complex object', the threshold for a SVHC must be applied to both the product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling based on the new ECHA "Guidance on requirements for substances in articles" (June 2017, version 4.0) and will be updating its statements accordingly.

Also in the Series | Alcoswitch ASE/F



Customers Also Bought

TE Part # 1825010-8 TE Internal #: 1825010-8





TE Part #2-796608-1 6WWV-09-008=#6 TRIBARRIER



TE Part #2-796608-3 6WWV-15-008=#6 TRIBARRIER



TE Part #1-328690-2 JAM NUT, GOLD PLATED




TE Part #104432-1 02 MODII HDR DRST B/A W/HD



TE Part #1986563-4 SSB7TP040402=TERM **BLOCK ASSY**



TE Part #7-146267-0 40 MODII HDR DRST B/A 100 W/HD



TE Part #5-5102084-7 18 MODII HORZ DR CE EESS 100CL



TE Part #6-1825011-4 ASF62RG04=6PDT AUTOSLIDE



TE Part #2176307-1 RP 1E 0.1W 12K4 0.1% 25PPM 5K RL



TE Part #4-2176307-6 RP 1E 0.1W 36K5 0.1% 25PPM 5K RL

Documents

Product Drawings

ASE22S04=DPDT AUTOSLIDE

English

CAD Files

Customer View Model

ENG_CVM_CVM_1825010-8_C.2d_dxf.zip

English

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1825010-8_C.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1825010-8_C.3d_stp.zip

English

Datasheets & Catalog Pages

SWITCHES_CORE_PROGRAM_CATALOG

ASE22S04=DPDT AUTOSLIDE

TE Part # 1825010-8 TE Internal #: 1825010-8



English