

Control Connectors

| POLES | FACE VIEW MALE | WIRING CODE | AWG CABLE SIZE | RATING 600V 60°C | LEAD LENGTH ft | PLUGS | | RECEPTACLES W/SCREW TERMINATION | |
|-------|----------------|---|----------------|------------------|----------------|-------|--------|---------------------------------|--------|
| | | | | | | MALE | FEMALE | MALE | FEMALE |
| 3 | | 1-GREEN 2-BLACK 3-WHITE 4-NO CONNECTION | #12 | 25A | 6 | 32902 | 32095 | 32911 | 32901 |
| | | | | | 12 | 32903 | 32906 | | |
| 4 | | 1-GREEN 2-BLACK 3-WHITE 4-RED 5-NO CONNECTION | #12 | 20A | 6 | 33204 | 33206 | 33202 | 33201 |
| | | | | | 12 | 33203 | 33207 | | |
| 5 | | 1-GREEN 2-ORANGE 3-BLACK 4-WHITE 5-RED | #12 | 16A | 6 | 33504 | 33509 | 33505 | 33501 |
| | | | | | 12 | 33502 | 33510 | | |
| 6 | | 1-GREEN 2-ORANGE 3-BLUE 4-BLACK 5-WHITE 6-RED | #12 | 16A | 6 | 33804 | 33809 | 33806 | 33801 |
| | | | | | 12 | 33802 | 33810 | | |
| | | | #14 | 12A | 6 | 33807 | 33812 | | |
| | | | | | 12 | 33805 | 33813 | | |
| 7 | | 1-GREEN 2-ORANGE 3-BLUE 4-WHT W/BLK TR. 5-BLACK 6-WHITE 7-RED | #12 | 16A | 6 | 34109 | 34119 | 34110 | 34101 |
| | | | | | 12 | 34106 | 34120 | | |
| | | | #14 | 12A | 6 | 34111 | 34122 | | |
| | | | | | 12 | 34132 | 34123 | | |
| 8 | | 1-GREEN 2-ORANGE 3-BLUE 4-WHT W/BLK TR. 5-RED W/BLK TR. 6-BLACK 7-WHITE 8-RED | #12 | 14A | 6 | 34404 | 34415 | 34421 | 34401 |
| | | | | | 12 | 34405 | 34416 | | |
| | | | #14 | 11A | 6 | 34406 | 34418 | | |
| | | | | | 12 | 34407 | 34416 | | |
| 9 | | 1-GREEN 2-ORANGE 3-BLUE 4-WHT W/BLK TR. 5-RED W/BLK TR. 6-GREEN W/BLK TR. 7-BLACK 8-WHITE 9-RED | #12 | 14A | 6 | 34714 | 34725 | 34716 | 34701 |
| | | | | | 12 | 34713 | 34726 | | |
| | | | #14 | 11A | 6 | 34717 | 34728 | | |
| | | | | | 12 | 34718 | 34729 | | |
| 10 | | 1-GREEN 2-ORANGE 3-BLUE 4-WHT W/BLK TR. 5-RED W/BLK TR. 6-GREEN W/BLK TR. 7-ORANGE W/BLK TR. 8-BLACK 9-WHITE 10-RED | #12 | 14A | 6 | 65005 | 65015 | 65014 | 65001 |
| | | | | | 12 | 65003 | 65017 | | |
| | | | #14 | 11A | 6 | 65006 | 65018 | | |
| | | | | | 12 | 65004 | 65019 | | |
| 11 | | 1-GREEN 2-ORANGE 3-BLUE 4-WHT W/BLK TR. 5-RED W/BLK TR. 6-GREEN W/BLK TR. 7-ORANGE W/BLK TR. 8-BLUE W/BLK TR. 9-WHITE 10-BLACK 11-RED | #12 | 10A | 6 | 65303 | 65315 | 65308 | 65301 |
| | | | | | 12 | 65302 | 65316 | | |
| | | | #14 | 7A | 6 | 65305 | 65318 | | |
| | | | | | 12 | 65306 | 65319 | | |
| 12 | | 1-GREEN 2-ORANGE 3-BLUE 4-WHT W/BLK TR. 5-RED W/BLK TR. 6-GREEN W/BLK TR. 7-ORANGE W/BLK TR. 8-BLUE W/BLK TR. 9-WHITE 10-BLACK 11-RED 12-BLK W/WHT TR. | #12 | 10A | 6 | 35622 | 35629 | 35620 | 35601 |
| | | | | | 12 | 35610 | 35630 | | |
| | | | #14 | 7A | 6 | 35653 | 35632 | | |
| | | | | | 12 | 35654 | 35633 | | |

Note: 11 pole plug use 12 conductor cord (black/white tr. not used)