

MRJ3404 Product Details

 Share  Print  Email



MRJ3404

TE Internal Number: 1825535-3

 [Active](#)

Rotary Switches

 [Always EU RoHS/ELV Compliant \(Statement of Compliance\)](#)

Product Highlights:

- 12 Positions
- Angle of Throw = 30.00 °
- Actuator Style = Long Thin Knob
- Code Type = 3 Poles
- Straight Mount Angle

[View all Features](#)

Quick Links

- [Check Pricing & Availability](#)
- [Search for Tooling](#)
- [Product Feature Selector](#)
- [Contact Us About This Product](#)

 [Add to My Part List](#)  [Request Sample](#)  [Find Similar Products](#)  [Buy Product](#)

Documentation & Additional Information

Product Drawings:

- [MINIATURE ROTARY SWITCH 12 POS.-30%-%d DETENT \(MRJ SE...](#) (PDF, English)

Catalog Pages/Data Sheets:

- None Available

Product Specifications:

- None Available

Application Specifications:

- None Available

Instruction Sheets:

- None Available

CAD Files:

- None Available

Additional Information:

- [Product Line Information](#)

Related Products:

- [Tooling](#)

[List all Documents](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- [Angle of Throw \(°\)](#) = 30.00
- [Actuator Style](#) = Long Thin Knob
- [Code Type](#) = 3 Poles
- [Mount Angle](#) = Straight
- Product Series = MRJ

Electrical Characteristics:

- Contact Rating = 0.4 VA max @ 20 VDC or peak AC

Termination Features:

- Solder Tail Contact Plating = Gold over Nickel

Body Features:

- [Number of Positions](#) = 12

Contact Features:

- Contact Base Material = Brass

Housing Features:

- Housing Material = Epoxy

Industry Standards:

- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Wave solder capable to 240°C, Wave solder capable to 260°C, Wave solder capable to 265°C
- RoHS/ELV Compliance History = Always was RoHS compliant

Other:

- Brand = Alcoswitch
- Comment = Adjustable

Corporate Information

[Who We Are](#)
[Investors](#)
[News Room](#)
[Supplier Portal](#)
[Careers](#)

Quick Links

[Check Distributor Inventory](#)
[Cross Reference](#)
[Find Documents & Drawings](#)
[Product Compliance Support Center](#)
[Site Map](#)

Customer Support

[Email or Chat With Us](#)
[Find a Phone Number](#)
[Search Knowledge Base](#)
[Manage your Account](#)

Keep Me Informed

Receive TE News, Events & Technology Updates

Enter your email address

