



Products


Industries & Solutions

Search



Resources
Sign In ▾

[Relays, Contactors & Switches](#) > [Switches](#) > [Pushbutton Switches](#)



TE CONNECTIVITY (TE) AV19 DPL 0.4VA POWER LED RED 12V

Alcoswitch | Alcoswitch AV

AV1921P312R04
TE Internal Number: 6-2213766-6

EU RoHS Compliant

EU ELV Compliant

Configuration (Pole-Throw) **Double Pole - Double Throw**

Number of Actuators **Single**

Bushing Style **Threaded**

Illuminated **Yes**

Process Sealed **Yes**

[See All Features](#)

✓ Active

↓ **PRODUCT DRAWING**
English

↓ **3D PDF**

> [See All Documentation](#)

North America ▾

Contact us to request pricing, availability and customization options.

REQUEST ADDITIONAL INFORMATION



GET SAMPLE



SAVE TO LIST ▾



FIND SIMILAR PRODUCTS



DOCUMENTATION

FEATURES

PRODUCT COMPLIANCE

Product Drawings

[ANTI-VANDAL SWITCH 19mm POWER LOGO LED](#)

PDF

English

CAD Files

[3D PDF](#)

PDF

3D

[Customer View Model](#)

2D_DXF.ZIP

English

[Customer View Model](#)

3D_IGS.ZIP

English

[Customer View Model](#)

Agency Approvals

UL Report

[Anti Vandal Switches](#)

PDF

English

Please review product documents or [contact us](#) for the latest agency approval information. Please Note: Use the Product Drawing for all design activity.

Product Type Features

Dust Proof	Yes
Illuminated	Yes
Actuator Style	Round
Product Type	Switch
Switch Type	Pushbutton

Configuration Features

Configuration (Pole-Throw)	Double Pole - Double Throw
Number of Actuators	Single
Snap Action	Without
Support Bracket	Without
Tactile	No
Operating Function	Push-On/Push-Off
Detent Style	Audible
ESD Grounding Terminal	Without

Electrical Characteristics

Voltage Rating (VAC)	250
----------------------	------------

Body Features

Case Material	PBT
Bushing Style	Threaded
Actuator Profile	Flush

Contact Features

Contact Current Rating (A)	.4
Contact Plating	Gold

Termination Features

Termination Type	Wire Lugs
------------------	------------------



Mechanical Attachment	Mounting Type	Panel
	Mounting Angle	Vertical
Housing Features	Process Sealed	Yes
Dimensions	Bushing Length (in)	19
Statement of Compliance	Statement of Compliance PDF	

Compatible Products





[Contact Product Support](#)

Also in the Series | [Alcoswitch AV](#)



Pushbutton Switches
(966)

Customers Also Bought

<p>RIBBON CABLE CONNECTORS</p>	<p>TERMINAL BLOCK HEADERS & RECEPTACLES</p>	<p>CARD EDGE POWER CONNECTORS</p>	<p>SWITCH KNOBS</p>
			
<p>16P.MICRO-MATCH MOB 8-215464-6</p>	<p>2 POS 5.08MM R/A PLUG, TRM BLK 796635-2</p>	<p>CONN SEC II 15 POS 100C/L 5530841-2</p>	<p>PKB70B1/4=KNOB PLASTIC W/SKIRT PKB70B1/4</p>

Events

TE News Center

Careers

Investors

Corporate Responsibility

Terms and Conditions of Sale

Suppliers



Find Authorized Distributors



What's New on TE.com



Product FAQs

United States (EN)

Germany (DE)

China (中文)

Japan (日本語)

Afghanistan (EN) ▼

Find Your Country ▼

[Terms of Use](#) | [Privacy](#) | [Cookie Policy](#) | [Accessibility](#) | [Site Map](#)



© 2017 TE Connectivity Corporation. All Rights Reserved