

[Skip to content](#)

[Corporate Home](#) | [Electronic Components](#) | [Segments](#) | [Who We Are](#)

Worldwide



Our commitment. Your advantage.

Search

By:



[Sign In](#) | [Register \(Why Register?\)](#)

[Products](#)



- Connectors
- Electromechanical Components
- Electronic Modules
- Fiber Optics
- Filters
- Identification Labeling Products
- Passive Components
- Power Sources
- RF & Microwave Products
- Tooling Products
- Touch Screen Displays
- Tubing, Molded and Harnessing Products
- Wire, Cable and Cable Assemblies
- List all Product Types



- [Aerospace & Defense](#)
- [Appliance](#)
- [Automotive](#)
- [Communications](#)
- [Computer & Consumer Electronics](#)
- [Industrial & Commercial](#)
- [Instrumentation & Medical Equipment](#)

[By Brand](#)

[A to Z](#)

[Documentation](#)

[Find](#)

- [Documents & Drawings](#)
- [Find CAD Models](#)
- [SPICE/Electrical Models](#)
- [NAFTA Certificate of Origin](#)
- [White Papers](#)

[Resources](#)

[RoHS](#)

- [Compliance & Alternates](#)
- [Cross Reference Products](#)
- [Compare Multiple Products](#)
- [Check Distributor Inventory](#)
- [Find Authorized Distributors](#)

[My Account](#)

[Sign In](#)

[Register](#)

[Customer Support](#)

[Support](#)

- [RoHS Support Center](#)
- [Glossary of Terms](#)
- [eBulletin Newsletter](#)

[Home](#) > [Products](#) > [By Type](#) > [Switches](#) > [Product Feature Selector](#) > Product Details

MSP103B04 Product Details



MSP103B04

✓ [Active](#)

Pushbutton Switches

 [Always EU RoHS/ELV Compliant \(Statement of Compliance\)](#)

Product Highlights:

- Switch
- Not Tactile
- Single Pole - Single Throw Configuration (Pole-Throw)
- Contact Rating = 3A
- Operating Function = Normally Closed, Momentary

[View all Features](#)

Quick Links

- [Check Pricing & Availability](#)
- [Search for Tooling](#)
- [Product Feature Selector](#)
- [Contact Us About This Product](#)

Documentation & Additional Information

Product Drawings:

- [SWITCH, PUSHBUTTON MSP103, SILVER](#) (PDF, English)

Catalog Pages/Data Sheets:

- None Available

Product Specifications:

- None Available

Application Specifications:

- None Available

Instruction Sheets:

- None Available

CAD Files:

- None Available

Additional Information:

- [Product Line Information](#)

Related Products:

- [Tooling](#)

[List all Documents](#)

Product Features (Please use the Product Drawing for all design activity)**Product Type Features:**

- Product Type = Switch
- Tactile = No
- Configuration (Pole-Throw) = Single Pole - Single Throw
- Mount Angle = Vertical
- Termination Type = Wire Lugs
- Actuator Style = Round

Electrical Characteristics:

- Contact Rating = 3A

Body Related Features:

- [Series](#) = MSP3
- Mount Style = Panel
- Actuator Length (mm [in]) = 2.50 [0.098]
- Actuator Profile = Extended
- Actuator Color = Black
- Bushing Diameter = 1/4-40
- Case Material = Thermoplastic (LCP)
- Actuator Material = Thermoplastic

Contact Related Features:

- Contact Plating = Silver
- Contact Material = Copper Alloy

Housing Related Features:

- Process Sealed = No
- Low Profile = No
- Bushing Style = Threaded

Configuration Related Features:

- Operating Function = Normally Closed, Momentary
- Ganged = No
- ESD Grounding Terminal = Without
- Number of Actuators = Single
- Illuminated = No
- Dust Proof = No
- Support Bracket = Without
- Snap Action = Without
- Bushing Length (mm [in]) = 5.97 [0.235]

Industry Standards:

- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Hand solderable with lead free solder
- RoHS/ELV Compliance History = Always was RoHS compliant

Conditions for Usage:

- Temperature Rating = Standard

Packaging Related Features:

- Packaging Method = Loose Piece

Other:

- Brand = Alcoswitch

[Provide Website Feedback](#) | [Contact Customer Support](#)

[Home](#) | [Customer Support](#) | [Suppliers](#) | [Site Map](#) | [Privacy Policy](#) | [Browser Support](#)

© 2007 Tyco Electronics Corporation All Rights Reserved

