




## TXR40AB00-1210AI2 Product Details

[Share](#) | [Print](#) | [Email](#)


### Braid, Fixed, Spin and Tinel Lock Adapters

[Not EU RoHS or ELV Compliant](#)

#### Product Highlights:

- Style = Tinel Lock Braided
- Connector Code = 40
- Straight
- Shell Size = 13, C
- Entry Size = 10

[View all Features](#)

**TXR40AB00-1210AI2**

TE Internal Number: 972687-000

 [Active](#)

[Add to My Part List](#)
 [Request Sample](#)
 [Find Similar Products](#)
 [Buy Product](#)

#### Quick Links

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

### Documentation & Additional Information

#### Product Drawings:

- [T-FIT Adapter and Molded Parts Boot Kits](#) (PDF, English)
- [Tinel-Lock Adapter](#) (PDF, English)

#### Catalog Pages/Data Sheets:

- None Available

#### Product Specifications:

- None Available

#### Application Specifications:

- None Available

#### Instruction Sheets:

- None Available

#### CAD Files:

- None Available

#### Related Products:

- [Tooling](#)

[List all Documents](#)

### Product Features (Please use the Product Drawing for all design activity)

#### Product Type Features:

- [Style](#) = Tinel Lock Braided
- [Angle](#) = Straight
- [Shell Size](#) = 13, C
- Finish = Cadmium Plating over Electroless Nickel
- Material = Aluminum Alloy
- Color = Olive Drab

#### Electrical Characteristics:

- [Boot Diameter \(mm \[in\]\)](#) = 23.49 [0.925]
- [Entry Diameter \(mm \[in\]\)](#) = 15.90 [0.630]
- Finish Code = B

#### Body Features:

- [Connector Code](#) = 40
- [Entry Size](#) = 10
- [Cable Diameter \(Max.\) \(mm \[in\]\)](#) = 15.37 [0.605]

#### Configuration Features:

- [Braid](#) = Preattached Single 36 AWG Braid
- Material Code = A

#### Industry Standards:

- [RoHS/ELV Compliance](#) = Not ELV/RoHS compliant
- [Lead Free Solder Processes](#) = Not relevant for lead free process

#### Other:

- Brand = Raychem

### Corporate Information

[Who We Are](#)

[Investors](#)

[News Room](#)

[Supplier Portal](#)

[Careers](#)

### Quick Links

[Check Distributor Inventory](#)

[Cross Reference](#)

[Find Documents & Drawings](#)

[Product Compliance Support Center](#)

[Site Map](#)

### Customer Support

[Email or Chat With Us](#)

[Find a Phone Number](#)

[Search Knowledge Base](#)

[Manage your Account](#)

### Keep Me Informed

Receive TE News, Events & Technology Updates

Enter your email address

