



What can we help you find?

- Products
- Industries
- Resources
- About TE
- My Account
- Innovation
- Support Center

Home > Products > Pin & Socket Connectors > Product Feature Selector > Product Details

STM015C5Q Product Details

Share Print Email



STM015C5Q
(1-1589482-7)

TE Internal Number: 1-1589482-7

Active

Nanominiature DUALOBE® Connectors & Jumper Assemblies

Not EU RoHS or ELV Compliant

Product Highlights:

- Connector
- Preloaded
- Connector Style = Plug
- Number of Rows = 2
- 15 Positions

[View all Features](#)

[Add to My Part List](#) [Request Sample](#) [Find Similar Products](#) [Buy Product](#)

Quick Links

- ▶ [Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

Documentation & Additional Information

<p>Product Drawings:</p> <ul style="list-style-type: none"> • PLUG ASSEMBLY, VERTICAL MOUNT, THROUGH HOLE, 2 TO 4 ... (PDF, English) <p>Catalog Pages/Data Sheets:</p> <ul style="list-style-type: none"> • 1589482 Nanonics Cross Reference (PDF, English) <p>Product Specifications:</p> <ul style="list-style-type: none"> • None Available <p>Application Specifications:</p> <ul style="list-style-type: none"> • None Available <p>Instruction Sheets:</p> <ul style="list-style-type: none"> • None Available <p>CAD Files:</p> <ul style="list-style-type: none"> • None Available 	<p>Additional Product Images:</p> <ul style="list-style-type: none"> • Product Photo <p>Related Products:</p> <ul style="list-style-type: none"> • Tooling
--	--

[List all Documents](#)

Product Features (Please use the Product Drawing for all design activity)

<p>Product Type Features:</p> <ul style="list-style-type: none"> • Product Type = Connector • Termination Style = Printed Circuit Board • PCB Mount Style = Through Hole <p>Mechanical Attachment:</p> <ul style="list-style-type: none"> • Mounting/Mating Hardware = With • Hardware Type = 1.2 mm Captive Jackscrew <p>Electrical Characteristics:</p> <ul style="list-style-type: none"> • Surface Mount Extended Leads = Without <p>Termination Features:</p> <ul style="list-style-type: none"> • Tail Length (mm [in]) = 2.29 [0.09] <p>Body Features:</p> <ul style="list-style-type: none"> • Mount Orientation = Vertical 	<p>Housing Features:</p> <ul style="list-style-type: none"> • Connector Style = Plug • Housing Material = Aluminum • Housing Plating = Nickel <p>Configuration Features:</p> <ul style="list-style-type: none"> • Preloaded = Yes • Number of Rows = 2 • Number of Positions = 15 <p>Industry Standards:</p> <ul style="list-style-type: none"> • RoHS/ELV Compliance = Not ELV/RoHS compliant • Lead Free Solder Processes = Not suitable for lead free processing <p>Other:</p> <ul style="list-style-type: none"> • Brand = Nanonics
--	--

Corporate Information

- [About TE](#)
- [Investors](#)
- [News Room](#)
- [Supplier Portal](#)
- [Careers](#)
- [Terms & Conditions](#)
- [Privacy Policy](#)

Quick Links

- [Distributor Inventory](#)
- [Product Cross Reference](#)
- [Documents & Drawings](#)
- [Product Compliance Support Center](#)
- [Site Map](#)

Customer Support

- [Email or Chat With Us](#)
- [Find a Phone Number](#)
- [Knowledge Base](#)
- [Manage Your Account](#)

Keep Me Informed

Receive TE News, Events & Technology Updates

Enter your email address

