


AVIATOR 54" Flush Mounted Fan

FH-W1811-54

MODERN FORMS SMART FANS



PRODUCT DESCRIPTION

Inspired by the golden age of flying, this smart fan takes technology to the next level. Pair it with the exclusive Modern Forms app to save on energy costs and intuitively create schedules that adapt to your behavior. Two simulated wood finishes contrast with the matte black or graphite housings for an understated look in interior or exterior spaces. Available option LED light kit sold separately.

SPECIFICATIONS

Construction: Aluminum
Blade: 13° Pitch, 54" sweep, ABS
Wire: 32"
Hanging Weight: 12.5 lbs
Total Power: 27W
Standards: UL/cUL Wet Location listed, Compliant, Title 20, Energy Star rated

FEATURES

- 6 fan speeds through both Summer and Winter Modes
- Silent DC motor
- Optional LED light kit sold separately
- Includes BT remote control with wall cradle
- Optional BT wall control sold separately
- Compatible with Modern Forms app

WIRELESS PERFORMANCE

Bluetooth Control Range: Up to 150 ft from fan
Wi-Fi Range: Up to 150 ft*

ESTIMATED AIR PERFORMANCE

Airflow: 6744 cubic ft per minute on high
Power: 27 watts on high
Airflow Efficiency: 250 cubic ft per minute per watt
RPM: 170 RPMs on high

ORDER NUMBER

Model	Housing	Blade
FH-W1811-54	GH Graphite	WG Weathered Gray
	MB Matte Black	DK Distressed Koa
	MB Matte Black	Matte Black

OPTIONAL LUMINAIRE (Sold Separately)

Model	Finish
F-1811-LED	GH Graphite
	MB Matte Black

Example: F-1811-LED-GH

Example: FH-W1811-54-GH/DK

*Results may vary based on application and surroundings.



modernforms.com
 Phone (866) 810.6615
 Fax (800) 526.2585

Headquarters/Eastern Distribution Center
 44 Harbor Park Drive
 Port Washington, NY 11050

Central Distribution Center
 1600 Distribution Ct
 Lithia Springs, GA 30122




Western Distribution Center
 1750 Archibald Avenue
 Ontario, CA 91760

AVIATOR 54" Flush Mounted Fan

FH-W1811-54

MODERN FORMS
SMART FANS

OPTIONAL ACCESSORIES

BT Wall Control 	F-WCBT	WT White	Control fan speed, light brightness and switch between Summer and Winter Modes from up to 150ft away. One BT Wall Control comes standard with this fan.
BT Remote Control 	F-RCBT	WT White	Sold separately. Control fan speed and light brightness, and switch between Summer and Winter Modes from up to 150 ft away. Includes easy-to-install cradle and batteries.
Wi-Fi Touch Panel Wall Control 	F-TS	BK Black WT White	Sold separately. Android tablet comes pre-loaded with Modern Forms app, Wi-Fi range up to 150 ft from router. Results may vary based on application/surroundings.

Examples: RF Wall Control - **F-WC-WT**, RF Remote Control - **F-RC-WT**, Wi-Fi Touch Panel - **F-TS-WT**

modernforms.com
Phone (866) 810.6615
Fax (800) 526.2585

Headquarters/Eastern Distribution Center
44 Harbor Park Drive
Port Washington, NY 11050

Central Distribution Center
1600 Distribution Ct
Lithia Springs, GA 30122

Western Distribution Center
1750 Archibald Avenue
Ontario, CA 91760