

Item Number 7305200

Drake Ceiling Fan

48 in. Gun Metal Finish
Reversible Blades (Weathered Oak/Walnut) Opal Frosted Glass

Specifications

Size	48"
Blades.....	Reversible Plywood Blades (Weathered Oak/Walnut)
Blade Pitch.....	13°
Approved Location	Indoor
Suggested Room Size.....	Large Room (up to 15x15)
Down Rod.....	3/4 x 4"
Installation.....	Down Rod Only
Max. Ceiling Angle.....	N/A
Lead Wire	54"
Light Bulb Usage.....	Includes 16 Watt Integrated LED
Control	Remote Control Included
Motor Finish.....	Gun Metal
Motor Material	Silicon Steel Motor 153mm x 17mm
Reverse Airflow.....	Yes
Capacitor	Dual
Switch Housing Cap.....	Not Included



Reversible Walnut
Finish Blades

Energy Information

	<u>With down rod</u>	<u>Hugger/ Without down rod</u>
Airflow (CFM) when operated at high speed.....	5055	N/A
Energy Use (excludes lights) ^Δ	39	N/A
Airflow (CFM) ^Δ	3597	N/A
Airflow Efficiency (CFM/W) ^Δ	92	N/A
Estimated Yearly Energy Cost ^Δ	\$11	N/A
RPM (High)	225	
Amp (High)	0.50	
Watts (High)	59	



Light Source

Number of Lamps.....	1
Energy Use (Watts) [†]	16
Equiv. Incand. Wattage [†]	75
Color Temperature (Kelvin).....	3000
Color Designation: Warm White	
Lumen [†]	1160
CRI.....	90
Average Rated Hours.....	25000
Life in Years ^{**†}	22.80
Estimated Yearly Energy Cost..	\$1.93

Specifications are subject to change without notice, please visit www.westinghouselighting.com for latest information.

® and Westinghouse are trademarks of Westinghouse Electric Corporation.
Used under license by Westinghouse Lighting. All Rights Reserved.

^Δ Based on typical use, excluding lights
^{*} Based on 12 cents per kWh and 6.4 hours use per day
[†] Values are per lamp
^{**} Based on 3hrs./day

Item Number 7305200

Drake Ceiling Fan

48 in. Gun Metal Finish
 Reversible Blades (Weathered Oak/Walnut) Opal Frosted Glass

A. Top of Canopy to Bottom of Blades	9.9"
B. Top of Canopy to Bottom of Switch House	12.3"
C. Top of Canopy to Bottom of Canopy	2.5"
D. Width of Motor Housing.....	7.9"
E. Width of Canopy.....	5.1"
F. Top of Canopy to Bottom of Glass.....	16.1"




If a Combo Style Fan with a 4" Down Rod is installed without the Down Rod, Subtract 3" from the Dimensions Listed (A, B, F).
 If a Combo Style Fan with a 6" Down Rod is installed without the Down Rod, Subtract 5" from the Dimensions Listed (A, B, F).

Warranty

Ceiling fans backed by our Limited Lifetime Warranty have a lifetime motor warranty and a 2-year warranty on all other parts.

Specifications are subject to change without notice, please visit www.westinghouselighting.com for latest information.

 and Westinghouse are trademarks of Westinghouse Electric Corporation. Used under license by Westinghouse Lighting. All Rights Reserved.