



# Replacement Cartridge

## Specification Sheet

Multi Purpose - SWX00325 > SWX00390

### Description

- > Organic Vapor & Acid Gas with P100 (Organic Vapor, Sulfur Dioxide, Hydrogen Chloride, Chlorine, All Particulates)
- > NIOSH Approved
- > APF 10\* when Qualitative Fit Testing is performed with either half mask or full facepiece
- > APF 50\* when Quantitative Fit Testing is performed with full facepiece only
- > Safety Works cartridges and filters are only compatible with Safety Works Half Mask and Full Facepiece

\*APF (Assigned Protection Factors) and product compatibility are only effective when the employer implements a continuing, effective respirator program as required by Section 29 CFR 1910.134, including training, fit testing, maintenance and use requirements.

OSHA's Standard for Respiratory Protection, 29 CFR 1910, 134, requires Employers to implement a change schedule for all canisters and cartridges when there is not an end of service life indicator on the cartridge or canister. The employer shall describe the respirator program the information and data relied upon and the basis for the canister and cartridge change schedule and the basis for reliance on the data. This schedule must be site specific and take into consideration worksite humidity, worker breathing rate as well as contaminant concentrations.



### Technical Data

Color	Yellow Label / Magenta
Packaging	SWX00325 - 1 pair per clamshells, 4 clamshells per case SWX00390 - 1 pair per bag, 12 bags per case
Case Dimensions	SWX00325 - 11.4" x 6.2" x 10.6" / 29.0cm x 15.7cm x 26.9cm SWX00390 - 14.6" x 8.6" x 8.4" / 37.1cm x 21.9cm x 21.3cm
Case Weight	SWX00325 - 3.3 lbs / 1.5 kg SWX00390 - 8.7 lbs / 4.0 kg
COO	Macau



RETAIL PACKAGED  
(SWX00325 - CLAMSHELL)



INDUSTRIAL PACKAGED  
(SWX00390 - BAG)

### Barcodes

Item	Clamshell/Bag	Case
SWX00325	848309010449	30848309010440
SWX00390	848309011330	20848309011334

SAFETY WORKS® A SUBSIDIARY OF PIP

800-262-5755 > 518-861-0144 fax > sales@pipusa.com > www.pipusa.com



This document and the information contained herein is the property of Protective Industrial Products, Inc. (PIP) and may not be used or reproduced without permission. Product users should conduct all appropriate testing or other evaluations to determine the suitability of PIP products for a particular purpose or use within a particular environment. PIP DISCLAIMS ALL WARRANTIES OTHER THAN AS EXPRESSLY PROVIDED.