

The Pro's Choice Since 1938

SAKRETE

Blacktop Repair Tube

For filling cracks in blacktop surfaces that are approximately 1/8 inch (3.2 mm) to 3/8 inches (9.5 mm) in width or less. Not for use in areas of prolonged contact with water. Weather-resistant after curing.

SAFETY:

READ and UNDERSTAND the Material Safety Data Sheet (MSDS) before using this product. WARNING: Wear protective clothing and equipment. See HMIS block. For emergency information, call CHEMTREC at 800-424-9300 or 703-527-3887 (outside USA). KEEP OUT OF REACH OF CHILDREN.

PREPARATION: (read all directions before starting work)

Clean all surfaces before application. Cleaned surfaces may be moist. Back-fill deep cracks with sand or foam backer-rod to within 3/8 inch (9.5 mm) of surface. Very small cracks should be slightly widened to permit penetration of caulk.

APPLICATION:

Cut tube nozzle to approximate width of bead desired and squeeze caulk into crack using standard caulking gun. Smooth and trim off excess caulk with moist putty knife or jointing tool while caulk is very fresh. Crack surfaces to be caulked, and caulking material must be above 50° F (10° C) and must remain so for 48-72 hours for proper curing. Temperature and relative humidity will affect curing time.

CURING:

Allow to air-cure for 48-72 hours prior to traffic.

CLEAN UP:

Cleans up with water prior to drying.

STORAGE:

Protect from freezing. Store between 35° F (1.7° C) and 100° F (37.7° C).

COVERAGE: Tube fills a crack approximately 1/4 inch (6.3 mm) x 1/4 inch by 25 feet (7.6 m) long.

SHELF LIFE: One year from date of manufacture.

PACKAGING: 10.3 Fluid Ounces (304 ml) - UPC: 7-64661-19711-9

ENVIRONMENTAL ADVISORY:

Uncured or crushed cured cement is an environmental hazard, which may adversely affect fish and wildlife. Dispose of construction debris containing cement, including empty bags, at a permitted municipal disposal firm. Do not use crushed concrete as a fill near an aquatic habitat.

CAUTION: May cause eye, skin and respiratory irritation. Avoid prolonged breathing of vapor. Use only with adequate ventilation and personal protective gear. Prolonged and repeated skin contact can cause irritation. FIRST AID: Contact with eyes: Flush thoroughly with water for 15 minutes and seek medical attention. Skin contact: Wash off with soap and water.

LIMITED PRODUCT WARRANTY

The manufacturer warrants that this product shall be of merchantable quality when used or applied in accordance with the manufacturer's instructions. This product is not warranted as suitable for any purpose other than the general purpose for which it is intended. This warranty runs for one (1) year from the date the product is purchased. ANY IMPLIED WARRANTY OF

MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE ON THIS PRODUCT IS LIMITED TO THE DURATION OF THIS WARRANTY. Liability under this warranty is limited to replacement of defective product or, at the manufacturer's option, refund of the purchase price. CONSEQUENTIAL AND INCIDENTAL DAMAGES ARE NOT RECOVERABLE UNDER THIS WARRANTY.

The SAKRETE Companies
866-SAKRETE
866-725-7383
www.sakrete.com

REV 3-10