

OFFICE TECHNOLOGY

HSM SECURIO

Quality.

Performance.

Versatility.

HSM SECURIO premium document shredders – Every detail is designed for security!

The advantages:

- Solid steel cutting heads are virtually free of wear and ensure permanently precise cutting quality
- Ideal alignment of all cutting unit components ensure trouble-free operation
- Energy Management and Control System (EMCS) saves valuable energy
- All motors are designed for continuous, reliable use
- Quiet Operation – whisper like shredding
- Automatic reverse rectifies paper jams
- Transparent front window allows you to view filling level



HSM®

Great Products, Great People.

HSM® SECURIO



| HSM Model Numer | HSM Part # | Cutting Size / Type | Cutting Capacity in sheets | Bin Capacity | Security Level DIN 32757-1 | Security Level DIN 66399 | Cutting Capabilities | Features |
|-------------------|------------|--------------------------|----------------------------|--------------|----------------------------|------------------------------|----------------------|----------------------------|
| SECURIO C16s | HSM1901 | 1/4" strip-cut | 16-18 | 6.6 | 2 | P-2 T-2 E-2 | | DE LW JS ZP QO ST |
| SECURIO C16c | HSM1902 | 5/32" x 1" cross-cut | 6-7 | 6.6 | 3 | P-4 T-4 E-3 F-1 | | DE LW JS ZP QO ST |
| SECURIO C18s | HSM1911 | 1/4" strip-cut | 19-20 | 6.6 | 2 | P-2 O-2 T-2 E-2 | | DE LW JS ZP QO ST |
| SECURIO C18c | HSM1913 | 5/32" x 1" cross-cut | 10-11 | 6.6 | 3 | P-4 T-4 E-3 F-1 | | DE LW JS ZP QO ST |
| SECURIO B22s | HSM1831 | 1/4" strip-cut | 22-24 | 8.7 | 2 | P-2 O-2 T-2 E-2 | | DE LW JS ZP QO ST |
| SECURIO B22c | HSM1833 | 1/8" x 1 1/8" cross-cut | 12-14 | 8.7 | 3 | P-4 T-4 E-3 F-1 | | DE LW JS ZP QO ST |
| SECURIO B24s | HSM1781 | 1/4" strip-cut | 28-30 | 9 | 2 | P-2 O-2 T-2 E-2 | | DE LW JS CD EM 90 ST QO CS |
| SECURIO B24c | HSM1783 | 3/16" x 1 1/8" cross-cut | 17-19 | 9 | 3 | P-4 O-3 T-4 E-3 F-1 | | DE LW JS CD EM 90 ST QO CS |
| SECURIO B26s | HSM1801 | 1/4" strip-cut | 28-30 | 14.5 | 2 | P-2 O-2 T-2 E-2 | | DE LW JS CD EM 90 ST QO CS |
| SECURIO B26c | HSM1803 | 3/16" x 1 1/8" cross-cut | 17-19 | 14.5 | 3 | P-4 O-3 T-4 E-3 F-1 | | DE LW JS CD EM 90 ST QO CS |
| SECURIO B32s | HSM1821 | 1/4" strip-cut | 28-30 | 21.7 | 2 | P-2 O-2 T-2 E-2 | | DE LW JS CD EM 90 ST QO CS |
| SECURIO B32c | HSM1823 | 3/16" x 1 1/8" cross-cut | 17-19 | 21.7 | 3 | P-4 O-3 T-4 E-3 F-1 | | DE LW JS CD EM 90 ST QO CS |
| SECURIO B32cL4 | HSM1822 | 1/16" x 9/16" cross-cut | 11-13 | 21.7 | 4 | P-5 T-5 E-4 F-2 | | DE LW JS CD EM 90 ST QO CS |
| SECURIO B34s | HSM1841 | 1/4" strip-cut | 35-37 | 26.4 | 2 | P-2 O-2 T-2 E-2 | | DE LW JS CD EM 90 ST QO CS |
| SECURIO B34c | HSM1843 | 3/16" x 1 1/8" cross-cut | 22-24 | 26.4 | 3 | P-4 O-3 T-4 E-3 F-1 | | DE LW JS CD EM 90 ST QO CS |
| SECURIO B35s | HSM1921 | 1/4" strip-cut | 40-42 | 34.3 | 2 | P-2 O-2 T-2 E-2 | | DE LW JS CD EM 90 ST QO CS |
| SECURIO B35c | HSM1923 | 3/16" x 1 1/8" cross-cut | 24-26 | 34.3 | 3 | P-4 O-3 T-4 E-3 F-1 | | DE LW JS CD EM 90 ST QO CS |
| SECURIO P36s | HSM1851 | 1/4" strip-cut | 47-49 | 38.3 | 2 | P-2 O-2 T-2 E-2 | | DE LW JS CD EM 90 ST QO CS |
| SECURIO P36c* | HSM1853 | 3/16" x 1 1/8" cross-cut | 29-31 | 38.3 | 3 | P-4 O-3 T-4 E-3 F-1 | | DE LW JS CD EM 90 ST QO CS |
| SECURIO P36L6OMDD | HSM1854M | 1/32" x 3/16" level 6 | 12-14 | 38.3 | 6 | P-7 O-6 T-6 E-5 F-3 | | DE JS CD EM 90 ST QO CS HS |
| SECURIO P40s | HSM1881 | 1/4" strip-cut | 58-60 | 40 | 2 | P-2 O-2 T-2 E-2 | | DE LW JS CD EM 90 ST QO CS |
| SECURIO P40c* | HSM1883 | 3/16" x 1 1/8" cross-cut | 35-37 | 40 | 3 | P-4 O-3 T-4 E-3 F-1 | | DE LW JS CD EM 90 ST QO CS |
| SECURIO P44s | HSM1871 | 1/4" strip-cut | 76-78 | 55 | 2 | P-2 O-2 T-2 E-2 | | DE LW JS CD EM 90 ST QO CS |
| SECURIO P44c* | HSM1873 | 3/16" x 2" cross-cut | 43-46 | 55 | 3 | P-4 O-3 T-4 E-3 F-1 | | DE LW JS CD EM 90 ST QO CS |

*Includes internal oiler

HSM of America, LLC
 419 Boot Road
 Downingtown, PA 19335
 www.hsmofamerica.com
 Customer Service 800.613.2110

| | |
|---|--|
| DE - Made in Germany | CD - Continuous Duty Motor |
| LW - Lifetime Warranty on Solid Steel Cutting Rollers | EM - Energy Management Control System |
| JS - JamStop Anti-Jam Technology | 90 - 90% Less Energy Used with SECURIO |
| ZP - Zero Power | ST - Quality Solid Steel Precision Cutting Heads |
| QO - Quiet Operation | CS - Comprehensive Safety System |
| HS - High Security Solution | |

This is a small representation of our SECURIO offering. Additional models and options available. Contact your HSM dealer or sales representative for more information.

All technical data and measurements are approximate values. Technical and optical modifications reserved.

3/2014 - 3/00084