

500000-2 ✓ ACTIVE

SPIRAP

TE Internal #: 500000-2


Cable Tie Mounts & Accessories, Cable Tie Tool, Spiral, Product

Width .125 in [3.18 mm], Polyethylene, Natural, SPIRAP

[View on TE.com >](#)



Wire & Cable > Wire & Cable Accessories > Cable Tie Mounts & Accessories



Wire & Cable Accessory Type: **Cable Tie Tool**

Wire & Cable Mounting Type: **Spiral**

Adhesive Back: **Without**

Product Width: **3.18 mm [.125 in]**

Primary Product Material: **Polyethylene**

Features

Product Type Features

Product Type	Cable Wrap
Wire & Cable Accessory Type	Cable Tie Tool

Body Features

Primary Product Material	Polyethylene
Primary Product Color	Natural

Mechanical Attachment

Wire & Cable Mounting Type	Spiral
Adhesive Back	Without

Dimensions

Overall Outside Diameter	3.18 mm [.125 in]
Bundle Range Diameter	1.6 – 12.7 mm [.063 – .5 in]
Product Width	3.18 mm [.125 in]

Packaging Features

Packaged Length	30.48 m [100 ft]
-----------------	------------------

Packaging Method

Box

Other

Comment

SPIRAP Hand Tool is included with each box.

Product Compliance

For compliance documentation, visit the product page on [TE.com](#)>

EU RoHS Directive 2011/65/EU

Compliant

EU ELV Directive 2000/53/EC

Compliant

China RoHS 2 Directive MIIT Order No 32, 2016

No Restricted Materials Above Threshold

EU REACH Regulation (EC) No. 1907/2006

Current ECHA Candidate List: JUNE 2022 (224)
 Candidate List Declared Against: JAN 2022 (223)
 Does not contain REACH SVHC

Halogen Content

Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free

Solder Process Capability

Not applicable for solder process capability

Product Compliance Disclaimer


This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts





Also in the Series | SPIRAP



Cable Tie Mounts & Accessories(19)

Documents

Product Drawings

[SPIRAP, 1/8" PE, NAT, 100 FT](#)

English

CAD Files

[3D PDF](#)

3D

Customer View Model

[ENG_CVM_CVM_500000-2_V.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_500000-2_V.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_500000-2_V.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[SPIRAP PLASTIC CABLE WRAP TECHNICAL DATA SHEET](#)

English