



Wire Protection & Management > Heat Shrink Shapes > Bushings & Bobbins



Bushings & Bobbins Product Type: **Bushing**

Product Width: **15.2 mm [.6 in]**

Molded Part Type: **Accessories**

Primary Product Material: **Modified Elastomer**

Pliancy: **Flexible**

Features

Product Type Features

Bushings & Bobbins Product Type	Bushing
Molded Part Type	Accessories

Body Features

Heat Shrink Component Accessory Color	Black
Primary Product Material	Modified Elastomer
Pliancy	Flexible

Dimensions

Length	101.6 mm[4 in]
Product Width	15.2 mm[.6 in]

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JUNE 2022 (224) SVHC > Threshold: Octamethylcyclotetrasiloxane (D4) (.24%)

Article Safe Usage Statements:

Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.

Halogen Content

Not Yet Reviewed for halogen content

Solder Process Capability

Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # CJ2087-000
[HL2010E-KIT-120V](#)

Also in the Series | RAYCHEM SEB

[Bushings & Bobbins\(5\)](#)



[Cable Transitions & Breakouts\(1\)](#)

Documents**Product Drawings**[SEB-D](#)

English

Datasheets & Catalog Pages[1654025_Sec4_SEB](#)

SEB-D

Bushings & Bobbins, Bushing, Width .6 in [15.2 mm], Accessories, Modified
Elastomer, Flexible, RAYCHEM SEB



English

[Harness Repair Products Quick Reference Guide](#)

English