



Arm lengths
up to 8'

Freestanding heights
up to 30'

Holds loads up
to 150,000 lbs.
per column

*Double-sided I-Beam
Cantilever Rack*

**Maximize Storage Capacity and Density,
While Improving Accessibility**
with Steel King's I-Beam Cantilever Rack


■ *The I-Beam Cantilever Rack can help you organize
virtually any type of heavy-duty, odd-shaped load –
freeing up floor space – saving time*

Steel King's new I-Beam Cantilever Rack maximizes storage capacity, density and eases accessibility while clearing floor space of stacked long, heavy, odd-shaped items such as piping, conduit, sheet metal, building materials, or spools of cable.

Easier to use.

With no need of a front column, Steel King's I-Beam Cantilever Rack is faster to load and unload than standard pallet racks. This design saves horizontal space normally lost to rack structure, reduces fork truck damage and saves time otherwise spent on double handling which is typical with cumbersome floor storage systems.

I-Beam Cantilever Rack



*Single-sided I-Beam
Cantilever Rack*

STEEL KING[®]

Flexibility

- Steel King's I-Beam Cantilever Rack has no front columns, offering immediate accessibility
- Freestanding heights up to 30'
- Flexibility to adjust base sizes to accommodate different arm requirements

Built for Strength

- Steel King's I-Beam Cantilever Rack has the capacity to hold loads up to nearly 80,000 lbs. on one side of the column. Actual capacity depends on the number and length of the arms used.
- Constructed of I-beam structural steel with a 50,000 psi minimum yield
- Arms are secured to the columns with grade 5 bolted connections
- Heavy arm connector plate holds rigid even under heavy loads
- Bases are bolted to columns

Custom Configuration Without a Custom Cost

- With its modular design, the I-Beam Cantilever Rack is easy to install, readily expandable and offers greater adjustability
- Arms are bolted independently to columns
- 4" vertical spacing allows flexibility to accommodate load capacity and position
- Varying arm lengths up to 8'
- Pre-punched connection holes enable easy arm installation, adjustment and leveling so the arms cannot "slip" out of position

Options and Accessories

Along with Steel King's standard, light duty and furniture-style cantilever racks, the I-Beam Cantilever Rack offers options and accessories to enhance its use:


- Roof brackets
- Removable pipe end stops
- Removable bolted end lips
- Welded lips at a variety of heights
- Saddles for decking support
- Core/axle saddles for rolls
- Wire deck and drop on pans for storage of odd lengths of bar, rounds, etc.

Your Steel King Distributor:



Colors

Choose from one of Steel King's 12 standard non-toxic, lead-free colors to color-code your racks by use or for aesthetics – or choose the optional durable, powder coat paint finish for better gloss, hardness, adhesion and greater resistance to fork truck impact, solvents and paints, than typical enamel paints.



STEEL KING

2700 Chamber St., Stevens Point, WI 54481
(715) 341-3120 • (800) 826-0203
Fax: (715) 341-8792

info@steelking.com • www.steelking.com