



## X60 Wipers

### Product Information

Code	Color	Ply	Sheet Size	Put-Up	Sheets/Pack	Packs/Case	Sheets/Case
34015	White	1	12.5" x 16.8"	BRAG* Box	1/180	1	180
34790	White	1	9.1" x 16.8"	POP-UP* Box	10/125	10	1250
34865	White	1	12.5" x 14.4"	¼ Fold	12/76	12	912
34770	White	1	11" x 23"	¼ Fold	9/100	9	900
34900	White	1	12.5" x 16.8"	Flat Sheet	6/150	6	900
35401	White	1	9.8" x 13.4"	Small Roll	12/130	12	1560
35411	Blue	1	9.8" x 13.4"	Small Roll	12/130	12	1560
35421	White	1	19.8" x 13.4"	Small Roll	6/130	6	780
35431	Blue	1	19.8" x 13.4"	Small Roll	6/130	6	780
34955	White	1	12.5" x 13.4"	Jumbo Roll	1/1100	1	1100
34965	Blue	1	12.5" x 13.4"	Jumbo Roll	1/1100	1	1100



### Physical Properties

The following are current, subject to change at any time without notice. Physical property data is as produced; subsequent storage conditions and the age of the product, which are beyond Kimberly-Clark's control, may affect the properties of the product as received. Test results of competitive product are single sample of the product provided by the customer.

Property	Target Value 34015, 34790, 34865, 34770	Target Value 34900	Target Value 35401, 35411, 35421, 35431, 34955, 34965
Water Capacity (g/4"x4")	4.0	4.0	4.0
Wet Taber (Pulp Side) – Trimmed	14	14	14
Wet Taber (Pulp Side) – Untrimmed	13	13	13
Caliper, single sheet (.000 in) Trimmed	18	18	18
Caliper, single sheet (.000 in) Untrimmed	19	19	19
CD Wet Grab	7.4	7.4	7.4
CD Dry Grab	6.59	6.59	6.59
MD Dry Grab	7.22	7.22	7.22
Moisture (Roll Avg.)	5	5	5
Moisture (Individual)	5	5	5
Mineral Oil Capacity (g/4"x4")	2.7	2.5	2.7
Post Consumer Waste (%)	0	0	0
Pre Consumer Waste (%)	0	0	0
Total Recycled Fiber (%)	0	0	0
Third Party Certification	NA	NA	NA
Meets EPA Standards for minimum PCW Content: Wipers 40%	NA	NA	NA



### Workmanship Requirements

Wipers shall be made in accordance with reasonable industry practice with respect to holes, tears, wrinkles, cleanliness, odors and foreign materials or dirt. Edges shall be cleanly cut.

Kimberly-Clark warrants that its products (1) comply with K-C's standard specifications as of the delivery date to K-C's authorized distributors/direct purchasers and are warranted for the following periods from end user's date of purchase (verified by valid sales receipt) (a) five years for Balder Technology auto darkening filters; (b) two years for all other auto darkening filters; and (c) one year for powered air purifying respirators; (2) comply with all K-C labeling representations; and (3) are manufactured in compliance with all applicable federal, state, and local laws in effect at the time and place of manufacture of the products. THIS WARRANTY IS IN LIEU OF ALL OTHER WARRANTIES, EXPRESS OR IMPLIED, INCLUDING ANY WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE. K-C is not liable for any kind of special, incidental, or consequential damages. K-C's liability for breach of contract, tort or other cause of action shall not exceed the product purchase price. Purchasers and users are deemed to have accepted the above warranty and limitation of liability, and cannot change the terms by verbal agreement or by any writing not signed by K-C. To the extent required by applicable law, K-C does not limit its liability for death/injury resulting from K-C's negligence.

©\*Trademarks of Kimberly-Clark Worldwide, Inc. or its affiliates. Marques déposées de Kimberly-Clark Worldwide, Inc. ou de ses filiales. © 2013 KCWW.