



PROFESSIONAL



PROFESSIONAL

## Blast Through Buildup

# Z-Tread Heavy-Duty Floor Stripper

Why spend so much time and effort stripping floors when this heavy-duty stripper does so much of the work for you? It's a low-foaming stripper that uses chemical action to remove multiple layers of floor finish with minimal manual labor. You simply rinse or mop away residue.

### Benefits:

- Quickly removes multiple coats
- No phosphates or ammonia
- Free-rinsing

### Applications:

- Schools
- Shopping malls
- Grocery stores
- Airports

### Directions for Use:

#### Floor stripping without agitation:

Dilute 1 part Z-Tread Heavy-Duty Stripper to 4 parts hot (130° - 150°F or 54° - 66°C) water. Spread solution generously over area to be stripped. Allow solution to soak for at least 5 - 8 minutes. Pick up solution completely with clean mop or wet vacuum. Rinse twice and allow to dry before applying finish.

#### Floor stripping with agitation:

Dilute 1 part Z-Tread Heavy-Duty Stripper to 4 parts hot (130° - 150°F or 54° - 66°C) water. Spread over area to be stripped and allow to soak 5 - 8 minutes. Agitate with a brush or stripping pad either manually or with a floor machine. Pick up solution completely with clean mop or wet vacuum. Be sure to remove any wheel tracks with a clean damp mop. Rinse twice and allow to dry before applying finish.



Base Code: R031

## Companion Products:

### Base Code

- Z-Tread High Solids Floor Finish .....R037
- Z-Tread UHS Floor Finish .....R036
- Z-Tread Neutral Floor Cleaner .....R034
- Z-Tread Floor Sealer .....R040



1-877-7ZEPRO | www.zepprofessional.com

Hard Floor Care

**Specifications:**

<b>Physical Form</b>	Liquid
<b>Color</b>	Clear, colorless
<b>Odor</b>	Mild
<b>pH</b>	12.1
<b>Specific Gravity</b>	0.98
<b>Flash Point (TCC)</b>	136°F (58°C)
<b>Boiling Point</b>	200°F (93°C)
<b>Shelf Life</b>	1 year minimum
<b>D.O.T. Shipping Label</b>	None

**Packaging Information:**

SKU	Package Quantity	Weight (lbs)	Length (")	Height (")	Width (")
R03124	4-1 gal/case	37	13.00	13.00	12.50
R03135	5 gal/case	44	12.00	14.50	12.00

**Safety:**

Please make sure you have read and understand the product label and MSDS before using this product. MSDSs are available at [www.zepprofessional.com](http://www.zepprofessional.com). Put on appropriate personal protective equipment. Store and use away from heat, sparks, open flame or any other ignition source. Avoid contact with eyes, skin and clothing. Do not breathe vapor or mist. Use with adequate ventilation. Do not ingest. Do not reuse container. Wash thoroughly after handling. Observe label precautions.

