

Item Number 7232000

Contempra IV Ceiling Fan

52 in. Brushed Nickel Finish
 Reversible Blades (Rosewood/Bird's Eye Maple) Frosted Ribbed Glass

Specifications

Size	52"
Blades	Reversible MDF Blades (Rosewood/Bird's Eye Maple)
Blade Pitch	11°
Approved Location	Indoor
Suggested Room Size	Large Room (up to 15x15)
Down Rod	N/A
Installation	Hugger
Max. Ceiling Angle	N/A
Lead Wire	12"
Light Bulb Usage	Includes (4) Candelabra (E12) Base, 4.5 Watt B11 LED Lamps
Control	Not Adaptable
Motor Finish	Brushed Nickel
Motor Material	Cold Rolled Steel Motor 153mm x 15mm
Reverse Airflow	Yes
Capacitor	Triple
Switch Housing Cap	Not Included



Reversible Bird's Eye Maple
Finish Blades

Energy Information


	With down rod	Hugger/ Without down rod
Airflow (CFM) when operated at high speed.....	N/A	4296
Energy Use (excludes lights) ^Δ	N/A	39
Airflow (CFM) ^Δ	N/A	3225
Airflow Efficiency (CFM/W) ^Δ	N/A	82
Estimated Yearly Energy Cost ^Δ	N/A	\$11
RPM (High)	166	
Amp (High)	0.51	
Watts (High)	61	



Light Source

Number of Lamps.....	4
Energy Use (Watts) [†]	4.50
Equiv. Incand. Wattage [†]	60
Light Appearance (Kelvin).....	2700
Lumen [†]	500
CRI.....	80
Average Rated Hours.....	15000
Life in Years ^{**†}	13.60
Estimated Yearly Energy Cost..	\$0.54

Specifications are subject to change without notice, please visit www.westinghouselighting.com for latest information.

 WESTINGHOUSE, and INNOVATION YOU CAN BE SURE OF are trademarks of Westinghouse Electric Corporation.
 Used under license by Westinghouse Lighting. All Rights Reserved.

^Δ Based on typical use, excluding lights
^{*} Based on 12 cents per kWh and 6.4 hours use per day
[†] Values are per lamp
^{**} Based on 3hrs./day

Item Number 7232000

Contempra IV Ceiling Fan

52 in. Brushed Nickel Finish
 Reversible Blades (Rosewood/Bird's Eye Maple) Frosted Ribbed Glass

A. Top of Canopy to Bottom of Blades	7.1"
B. Top of Canopy to Bottom of Switch House	8.1"
C. Top of Canopy to Bottom of Canopy	N/A
D. Width of Motor Housing.....	11.5"
E. Width of Canopy.....	N/A
F. Top of Canopy to Bottom of Glass.....	13"



If a Combo Style Fan with a 4" Down Rod is installed without the Down Rod, Subtract 3" from the Dimensions Listed (A, B, F).
 If a Combo Style Fan with a 6" Down Rod is installed without the Down Rod, Subtract 5" from the Dimensions Listed (A, B, F).

Warranty

Ceiling fans backed by our Limited Lifetime Warranty have a lifetime motor warranty and a 2-year warranty on all other parts.

Specifications are subject to change without notice, please visit www.westinghouselighting.com for latest information.

 WESTINGHOUSE, and INNOVATION YOU CAN BE SURE OF are trademarks of Westinghouse Electric Corporation.
 Used under license by Westinghouse Lighting. All Rights Reserved.