

# BlinkerPaddle<sup>®</sup> LED-enhanced Paddles

- Visible up to a mile away!
- 20 hours flashing on a single charge (rechargeable batteries and chargers included)
- 3-way switch (one or both sides flashing)
- Automatic shut off when paddle lowered below horizontal
- 18" and 24" sizes available with any message and any grade of reflective sheeting

Patented TAPCO BlinkerSign<sup>®</sup> technology is used to make hand-held sign paddles more visible. Eight super-bright LEDs on each face match the BlinkerPaddle<sup>®</sup> background color and shape, flashing in unison every second. Flashing dramatically increases the paddle visibility and drivers react faster. A BlinkerPaddle<sup>®</sup> is especially effective in rain, fog, snow, and during low light conditions.



## BlinkerPaddle® Features

- Light-weight design minimizes arm and wrist stress (18" paddle weighs less than 2 pounds)
- Thumb switch turns LEDs on for either (or both) sign faces
- LEDs Automatically shut off when paddle lowered below horizontal



## Applications

- Flagger
- Road crews
- Crossing guards
- Event parking

## Accessories

- 1 Black Cordura nylon carrying case. Fits two 18" or 24" paddles and all accessories.
- 2 Orange fiberglass staff, extends up to 9' 6"
- 3 Gray three-piece staff, 7' 2" when assembled
- 4 Rubber base for orange or gray staffs. Allows for hands-free BlinkerPaddle® display & rotation



Visit **Traffic and Parking** on YouTube for videos on these products and more.



Standard Specifications (subject to change without notice)

### Sign face

Sign Substrate	.040 high impact white Polystyrene
Reflective Sheeting	3M™ High Intensity Prismatic or DG3 Diamond Grade™
MUTCD Compliance	2009 MUTCD Section 6E.03 Retroreflectivity and Illumination

### Batteries and charging

Batteries	Three 1.2 volt rechargeable AA NiMH. 3.6 volts total. 1500 mAh capacity.
Battery Lifespan	5-7 years (dependent upon usage and temperature)
Battery charging	120v AC wall charger and 12v DC car charger (cigarette lighter outlet)

### LEDs

Flash Pattern	Single flash, 60 flashes per minute
LED color	Amber, orange, red

### Warranty

90 days from date of purchase

### Activation

Switch	Three-way push-button: Activate LEDs on side 1, activate LEDs on side 2 or activate LEDs on both sides simultaneously
Automatic ON/OFF	Non-mercury switch automatically turns the paddle on when held upright (LEDs flash). Automatically turns the paddle off when lowered below horizontal(LEDs turn off)



1-800-236-0112 • [www.tapconet.com](http://www.tapconet.com) • [blinkersales@tapconet.com](mailto:blinkersales@tapconet.com)

