



CHARGER* Head Protection

Codes: 20392, 20401, 20399, 20393, 20398, 20394, 20397, 20395, 20396, 20402, 20403, 20645

Product Information

New Ratchet Code	Ratchet Code	New Plastic Code	Plastic Code	Color	PMS Color	Qty
20392	3013362	20425	3013409	White		12/Box
20401	3013370	20427	3013411	Yellow	012C	12/Box
20399	3013369	20432	3013415	Green	3425C	12/Box
20393	3013363	20428	3013412	Blue	2935C	12/Box
20398	3013368	20431	3013414	Orange	1665C	12/Box
20394	3013364	20429	3013413	Red	1797C	12/Box
20397	3013367	20434	3013417	Gray	430C	12/Box
20395	3013365	20433	3013416	Hi-Viz Orange	811C	12/Box
20396	3013366	20426	3013410	Hi-Viz Lime	381C	12/Box
20402	3013371			Sky Blue	305C	12/Box
20403	3013372	20436	3013420	Neon Pink	806C	12/Box
20645	3014571	20652	3014709	Black		12/Box



Accessories/Replacement Parts

New Code	Old Code	Description	QTY
20422	3013403	4-point Ratchet Suspension	6/Box
20424	3013405	4 - point Plastic Suspension	12/Bag
14434	3000114	2 - point Chin Strap	12/Bag
18446	3009653	4 - point Chin Strap	12/Bag
14429	3000105	Replacement Sweatband	12/Bag
14944	3002441	382B Blade Mounted Cap Adapter with Spark Deflector	12
14946	3002443	337 Cord Mounted Cap Adapter	12
14948	3002445	137 Spring Mounted Cap Adapter	12
14390	3000032	Model C Spring Mounted Cap Adapter (backward facing)	12



Product Information

Property	Description
Impact Type	ANSI Z89.1 Type I
Electrical Class Rating	Class E (Electrical): 20,000 volts (phase to ground)
Reverse Donning	Yes
Identifying Marks	6 Ribs contouring toward back of hat
Decorating Capability	Front: Back: Left Side: Right Side
Standard Colors	12
Accessory Slots	Yes
Chin Strap Attachment	Yes - 4 attachment points on shell
Rain Trough	Yes
Weight	13.8 ounces Ratchet / 12.8 ounces Plastic
Shell Material	HDPE - high density polyethylene
Suspension Options	Ratchet & Plastic
Suspension Attachment points	4-Point
Head Sizes	6½ - 8
Incremental Sizing Unit	1/24 inch increments Ratchet
Vertical Adjustments	Yes - 2 settings
Crown Patch	No
Sweat Band Material	Flame Retardant Treated Fleecy Cotton
Replaceable Sweat Band	Yes

Workmanship Requirement:

Head protection shall be made in accordance with reasonable industry practice with respect to defects or dirt and contamination. Head Protection should be packaged as specified having described design, suspension and color in the appropriate quantity as listed. For additional information: 1-800-255-6401 or kimtech@kcc.com

Kimberly-Clark warrants that its products (1) comply with K-C's standard specifications as of the delivery date to K-C's authorized distributors/direct purchasers and are warranted for the following periods from end user's date of purchase (verified by valid sales receipt) (a) five years for Balder Technology auto darkening filters; (b) two years for all other auto darkening filters; and (c) one year for powered air purifying respirators; (2) comply with all K-C labeling representations; and (3) are manufactured in compliance with all applicable federal, state, and local laws in effect at the time and place of manufacture of the products. THIS WARRANTY IS IN LIEU OF ALL OTHER WARRANTIES, EXPRESS OR IMPLIED, INCLUDING ANY WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE. K-C is not liable for any kind of special, incidental, or consequential damages. K-C's liability for breach of contract, tort or other cause of action shall not exceed the product purchase price. Purchasers and users are deemed to have accepted the above warranty and limitation of liability, and cannot change the terms by verbal agreement or by any writing not signed by K-C. To the extent required by applicable law, K-C does not limit its liability for death/injury resulting from K-C's negligence.

®/*Trademarks of Kimberly-Clark Worldwide, Inc. or its affiliates. Marques déposées de Kimberly-Clark Worldwide, Inc. ou de ses filiales. © 2013 KCWW.



Exceptional
Workplaces®

Revised April 2013