

We've created a new standard in rugged, superior security Steel Underbed Boxes

Superior Security, Weather Resistance & More

- "Quick Release" Keyway Connectors on the door ends of the coated aircraft door support cables are easy to remove. Allows the door to drop down to a vertical position for easier access to load and unload equipment and tools
- 3-Point Locking System Locks the door at the top and both sides to resist break-ins. Rotating T-Handle has drill-resistant lock
- New V-Groove door frame, Bulb-Shaped EPDM weather stripping and beveled edge door create a tight, moisture-resistant seal
- Rugged Aluminum Hinge nearly eliminates corrosion and features new stainless steel rivet design for maximum durability and security.
- Cross Hatch Pattern and Lock Guard reinforce the door for incredible strength
- Wider, Taller Door Opening for quick and easy access



Door Drops To Vertical Position For Easier Access When Door Support Cables Are Disconnected

DELTA[®] PRO

The new Delta PRO Steel Underbed Boxes launch a new era in moisture resistance and accessibility. 12-Gauge Cold-Rolled Steel Door and 14-Gauge Steel Body stand up to the most rugged, toughest conditions on the road or around the farm. Mount them under the bed of any type of work truck or a trailer.

V-Groove Door Frame & Seal Design

- Reinforces the body and provides a wider surface on all sides of the door opening to seal out moisture and dust.



Tight Door Seal

- Beveled door edges fit tight against the V-Groove door frame. Cross hatch pattern and high-strength bolster for superior security and weather resistance.



Aluminum Hinge

- Rugged 16-Gauge Continuous Aluminum Hinge is 3/8" in diameter. 1" knuckles and 1/4" hinge pin offer superior strength and durability.



Drop Down Door

- Exclusive new design allows door to drop down out of the way for easier loading and unloading of large, heavy or awkward equipment.



3-Point Locking System

- Draws the reinforced, beveled edge door tight against the door opening. Turning the T-handle locks the door at top and both sides for superior strength.



Rotating T-Handle

- Leak-proof to prevent moisture from getting inside. Drill-resistant lock cylinder prevents break-ins and handle folds down inside recessed area.



Wider Door Opening

- Wider, Taller Door Opening for easier access to tools and equipment.



Support Cable & Connectors

- "Quick Release" Keyway Connectors attach support cables to the door. Connectors are easy to remove to allow the door to drop down.



Truck Storage Solutions

Steel Underbed Boxes



V-Groove Door Frame & Seal Design

Automotive Bulb-Shaped EPDM Weather Stripping

14-Gauge Steel Body

Aircraft-Quality Support Cables

One-Piece Lock Housing

3-Way Locking System

"Quick Release" Keyway Connectors

Stainless Steel Industrial Hinge Rivets

Continuous Aluminum Hinge

12-Gauge Cold-Rolled Steel Door



BLACK Underbed Boxes



DELTA PRO			Dimensions			Shipping Cubic Ft.	Approx. Shipping Weight Lbs.
Model #	Finish	Size	A	B	C		
14" Tall x 12" Deep BLACK Underbed Boxes							
1-001002	Black	24" Long	24"	14"	12"	3.0	51.0
1-002002	Black	36" Long	36"	14"	12"	4.5	68.0
18" Tall x 18" Deep BLACK Underbed Boxes							
1-003002	Black	18" Long	18"	18"	18"	4.1	56.5
1-004002	Black	24" Long	24"	18"	18"	5.4	70.0
1-005002	Black	30" Long	30"	18"	18"	6.7	81.0
1-006002	Black	36" Long	36"	18"	18"	8.1	91.5
1-007002	Black	48" Long	48"	18"	18"	10.7	118.0
1-008002	Black	60" Long	60"	18"	18"	13.4	142.0
1-009002	Black	72" Long	72"	18"	18"	16.0	168.0
24" Tall x 24" Deep BLACK Underbed Boxes							
1-011002	Black	30" Long	30"	24"	24"	11.5	100.0
1-012002	Black	36" Long	36"	24"	24"	13.8	114.0
1-013002	Black	48" Long	48"	24"	24"	18.3	148.0
1-014002	Black	60" Long	60"	24"	24"	22.8	176.0




Underbed Box Mounting Brackets
 18" x 18" — Model 228000
 24" x 24" — Model 229000

WHITE Underbed Boxes

DELTA PRO			Dimensions			Shipping Cubic Ft.	Approx. Shipping Weight Lbs.
Model #	Finish	Size	A	B	C		
14" Tall x 12" Deep WHITE Underbed Boxes							
1-001000	White	24" Long	24"	14"	12"	3.0	51.0
1-002000	White	36" Long	36"	14"	12"	4.5	68.0
18" Tall x 18" Deep WHITE Underbed Boxes							
1-003000	White	18" Long	18"	18"	18"	4.1	56.5
1-004000	White	24" Long	24"	18"	18"	5.4	70.0
1-005000	White	30" Long	30"	18"	18"	6.7	81.0
1-006000	White	36" Long	36"	18"	18"	8.1	91.5
1-007000	White	48" Long	48"	18"	18"	10.7	118.0
1-008000	White	60" Long	60"	18"	18"	13.4	142.0
1-009000	White	72" Long	72"	18"	18"	16.0	168.0
24" Tall x 24" Deep WHITE Underbed Box							
1-013000	White	48" Long	48"	24"	24"	18.3	148.0

Heavy-Duty 2" C-Channel Brackets For Mounting Underbed Boxes. Bracket Have Multiple Mounting Holes For Easy Installation. Sold In Pairs.



Delta Consolidated Industries, Inc.
 A Danaher Company
 PO Box 1846
 4800 Krueger Dr.
 Jonesboro, AR 72403

All information in this catalog is subject to change without notice.

© 2008 Delta Consolidated Industries, Inc.

For ordering, use part # LIT143

DELTA
 Truck Storage Solutions
 800-643-0084 www.deltastorage.com