

ART VERSION #: 2

ART REVISION DATE: 09/28/2016

FINAL ART DATE: 09/XX/2016

DIE LINE #: 4435 285 04200

MX PART #: 4435 285 04202


PHILIPS LIGHTING USA	
Brand	PHILIPS
Product Famil	WARM GLOW LED
Shape	BR40
Wattage	10w
Master Brand Template Ref.	4435 285 04201
SGS number	XXXXXXX
6NC #	457010
PKG PART #	4435 285 04202
DIE #	4435 285 04200
CRC #	CRC_XXXUS
Barcode No.	0 46677 45701 3
Operator(s)	ellen.e.smith@philips.com
VERSION No.	v2
Date	SEPT 28, 2016
Cyan	<input type="checkbox"/>
Magenta	<input type="checkbox"/>
Yellow	<input type="checkbox"/>
Black	<input type="checkbox"/>
Die	<input type="checkbox"/>
Date Check	
<input type="checkbox"/> Check briefing Traffic	
Artwork document	
<input type="checkbox"/> Legend	<input type="checkbox"/> Number of colors
<input type="checkbox"/> 12NC	<input type="checkbox"/> Trapping/Bleed
<input type="checkbox"/> Barcode	<input type="checkbox"/> Images hires
<input type="checkbox"/> Diecut	<input type="checkbox"/> Jobsizes
Approval	
<input type="checkbox"/> QC Lithographer	
<input type="checkbox"/> Product Manager	
<input type="checkbox"/> Traffic Manager	

372.6

481

56

160



Lighting Facts Per Bulb	
Brightness	800 lumens
Estimated Yearly Energy Cost	\$1.20
Based on 3 hrs/day, 11¢/kWh Cost depends on rates and use	
Life	22.8 years
Based on 3 hrs/day	
Light Appearance	Warm
2700 K	
Energy Used	10 watts

LIMITED WARRANTY for Consumers:
Philips warrants that this bulb will be free from defects in material and workmanship and will operate for 5 years based on up to 3 hours average usage per day/7 days per week, when used as directed. If this bulb does not conform to the warranty, Philips will send you, at its election, a replacement bulb or refund your original purchase price upon receipt of the returned bulb, register receipt and proof of purchase. Please call our toll-free number, write to Philips or send an email at the website below to find out how to return the bulb. This limited warranty does not cover bulbs subject to accident, neglect, abuse, misuse or acts of God. REPLACEMENT OR REFUND IS YOUR SOLE REMEDY. EXCEPT TO THE EXTENT PROHIBITED BY APPLICABLE LAW, ANY IMPLIED WARRANTIES ARE LIMITED IN DURATION TO THE DURATION OF THIS WARRANTY. LIABILITY FOR INCIDENTAL OR CONSEQUENTIAL DAMAGES IS HEREBY EXPRESSLY EXCLUDED. Some states do not allow exclusion of incidental or consequential damages, so the above limitation or exclusion may not apply to you. This warranty gives you specific legal rights, and you may also have other rights which vary from state to state.

LIMITED WARRANTY for Professional, Industrial/Commercial Customers and applications:
Philips warrants that this bulb will be free from defects in material and workmanship and will operate for 3 years based on lamp operation of 12 hours average usage per day/7 days per week, when used as directed. Visit http://www.usa.lighting.philips.com/connect/fools_literature/warranties.wpd for full details and restrictions.


NOTES: This device complies with Part 15 of the FCC Rules. Operation is subject to the following two conditions: (1) This device may not cause harmful interference, and (2) This device must accept any interference received, including interference that may cause undesired operation.

Any changes or modifications not expressly approved by the party responsible for compliance could void the user's authority to operate the equipment.

This Class B complies with Canadian ICES-005.

*At \$0.11 per kWh, this 10 watt, 800 lumen BR40 LED uses \$27.50 of electricity over its 25,000 hour life. This is a \$151.25 savings when compared to the \$178.75 required to run a 65 watt, 800 lumen, BR40 incandescent over the same period. Actual savings will vary depending on cost per kWh.

4435 285 04202
Model: 9290011558A
Ordering Code: 10BR40/LED/827-22/DIM 120V
Assembled in one or more of the following countries:
China, Mexico
Philips Lighting North America Corporation
200 Franklin Square Drive
Somerset, NJ 08873, USA
Questions or Comments:
1-800-555-0050
www.philips.com



WARNINGS AND CAUTIONS: Not for use in totally enclosed or recessed luminaires (fixtures). This device is not intended for use with emergency exit fixtures or emergency lights. Suitable for use with dimmers. Visit www.philips.com/dimmercompatibility to find up-to-date dimmer and lighting control compatibility information. Risk of electric shock - Do not use where directly exposed to water. Before replacing, turn off power and let lamp cool to avoid electrical shock or burn. Only install in operating environments between -4°F and +113°F (-20°C and +45°C).

PRECAUCIONES Y CUIDADOS: No debe utilizarse en luminarias empotradas o totalmente cerradas. Este dispositivo no está diseñado para usar como iluminación de emergencia o dentro de luminarios de señalización en salida de emergencia. Se pueden usar con atenuadores de luz. Visita www.philips.com/dimmercompatibility para encontrar la compatibilidad con atenuadores y controles de luz. Riesgo de choque eléctrico - No utilizar donde haya contacto directo con agua. Antes de reemplazar, apague la corriente eléctrica y enfríe la lámpara para evitar un choque eléctrico o incendio. Solo instalar en ambientes entre -4 grados F y +113 grados F (-20 grados Centígrados y 45 grados C.)

Información sólo para el mercado Mexicano
Lámpara LED Dirrecional BR40/10W
Tensión Eléctrica 120V~
Frecuencia 60Hz
Corriente Eléctrica 120mA
Vida Nominal 25,000 h

Ensamblado en alguno de los siguientes países:
México y/o China
Contenido 1 pieza

Distribuido por:
PHILIPS MEXICANA S.A DE C.V.
Av. La Palma No. 6
Col. San Fernando La Herradura
Huixquilucan Estado de México CP. 52784
R.F.C. PME-620620-E84

Línea de Atención al Cliente
01800 508 9000 | (55) 5269 9139
smartlight.mexico@philips.com
Garantía 5 años, para términos y condiciones consultar el siguiente link:
<http://www.lighting.philips.com/mx/connect/garantias.wpd>