

15 ft Monitor VGA Cable - HD15 MM

Product ID: MXT101MM15



This 15-foot VGA Video Monitor Cable features two HDB15 (male) connectors, providing a reliable VGA connection.

For best performance, this VGA extension cable is designed to be used with low-resolution applications. For applications that require higher resolutions, see our 15ft Coax VGA Cable (MXT105MMHQ).

MXT101MM15 is backed by a StarTech.com lifetime warranty and free lifetime technical support.

Certifications, Reports and Compatibility

Applications

- Connects a PC's VGA port to a switchbox
- Connect a VGA display to a VGA source

Features

- Supports low resolution applications
- Guaranteed reliability

Hardware

Warranty	Lifetime
Connector Plating	Nickel

Cable Jacket Material PVC - Polyvinyl Chloride

Cable Shield Material Aluminum-Mylar Foil with Braid

Connector(s)

Connector A VGA (15 pin, High Density D-Sub)

Connector B VGA (15 pin, High Density D-Sub)

Special Notes / Requirements

Note Pin number 9 is not populated on these connectors

Physical Characteristics

Color Gray

Wire Gauge 28 AWG

Cable Length 15.0 ft [4.6 m]

Product Length 15.0 ft [4.6 m]

Product Width 1.3 in [33 mm]

Product Height 0.6 in [15 mm]

Weight of Product 8.2 oz [231.5 g]

Packaging Information

Package Length 11.4 in [29.0 cm]

Package Width 5.7 in [14.5 cm]

Package Height 0.0 in [0.1 mm]

Shipping (Package) Weight 8.4 oz [239.0 g]

What's in the Box

Included in Package 15 ft VGA Monitor Cable HD15 MM

**Product appearance and specifications are subject to change without notice.*