

HDMI Video Over IP Gigabit LAN Ethernet Receiver for ST12MHDLAN - 1080p

Product ID: ST12MHDLANRX



This HDMI over IP Receiver works with the HDMI over IP Extender Kit (sold separately) and lets you extend an HDMI signal over your network. You can use additional receivers (sold separately) to distribute the HDMI signal to multiple locations and combine your remote displays to create a video wall.

In a point-to-multipoint setup, the HDMI over IP kit can be connected through an unmanaged or managed Gigabit LAN portal. You can connect one or multiple sources (transmitters) to multiple displays (receivers) over IP, using a managed Gigabit Ethernet switch (with IGMP). For additional scalability, you can combine up to 16 different kits.

For smaller-scale applications, the extender kit can be used as a point-to-point video extender. You can connect the transmitter and receiver units directly over Cat5 or Cat6 cabling for a small-scale, one-to-one HDMI extension up to 330 feet (100 meters).

The HDMI distribution kit features easy-to-use video control software that helps you manage your IP video distribution. The app is simple to set up with automatic hardware detection, and lets you switch video sources for each remote display. You can also intuitively create and manage a video wall for an impressive digital signage presentation to catch the attention of your audience.

The software is available on iOS for your iPhone or iPad, Android for your smartphone or tablet, and Google Chrome browser.

The HDMI over IP extender kit includes optional mounting hardware for a tidy installation. Ideal for high-definition applications, the extender supports 1080p video resolutions and digital stereo audio. Plus, because the extender uses standard non-proprietary Cat5e or Cat6 Ethernet cable with RJ45 connectors, it eliminates both the expense and hassle of running specialized cables. The extender also features an EDID copy function, which ensures native resolution and maximum compatibility with your display or projector for a convenient plug-and-play installation.

Download the StarTech.com Video Control software to manage your IP video distribution.

Note: If using more than 1 Transmitter, or more than 4 Receivers an IGMP / Managed Network Switch is recommended for optimal performance. Non-managed network switches may also limit the performance of other devices connected to the same network.

The ST12MHDLANRX is TAA compliant and backed by a StarTech.com 2-year warranty with free lifetime technical support.

Certifications, Reports and Compatibility

Applications

- Connect the HDMI source equipment to multiple displays in a point-to-multipoint configuration over a Gigabit Network using additional ST12MHDLANRX Receivers
- Place the display in a convenient viewing area, while the HDMI source equipment is placed elsewhere in a separate, secured environment
- Extend HDMI using existing infrastructure
- Run multiple transmitters and receivers over the network using a managed switch
- Display the same HDMI audio/video signal on multiple displays, for large scale digital signage applications

Features

- Highly scalable - output an HDMI signal to over 100 additional displays (requires additional ST12MHDLANRX Receiver units, sold separately)
- EDID emulation ensures maximum resolution and compatibility with your display or projector
- Stereo Audio
- Includes optional mounting hardware
- Connect through a Gigabit LAN Network, or Point-to-Point
- High Definition support for resolutions up to 1080p (1920x1080)

Hardware

| | |
|----------------|----------------------|
| Warranty | 2 Years |
| Ports | 1 |
| Cabling | Cat 5e UTP or better |
| Audio | Yes |
| Rack-Mountable | No |
| Daisy-Chain | Yes |

Performance

| | |
|-----------------------------|---|
| Max Distance | 100 m / 330 ft |
| Maximum Digital Resolutions | 1920x1200 @60Hz |
| Supported Resolutions | 1920 x 1200 1920 x 1080 1600 x 1200 |
| Wide Screen Supported | Yes |
| Audio Specifications | Stereo Audio |

Connector(s)

| | |
|------------------------|------------------------|
| Remote Unit Connectors | HDMI (19 pin) RJ-45 |
|------------------------|------------------------|

Indicators

| | |
|----------------|-------------------------------------|
| LED Indicators | Link OK / POWER Reset - Receiver |
|----------------|-------------------------------------|

Power

| | |
|---------------------|---------------------|
| Power Source | AC Adapter Included |
| Input Voltage | 100 - 240 AC |
| Input Current | 0.6 A |
| Output Voltage | 12V DC 12V DC |
| Output Current | 1.5 A |
| Center Tip Polarity | Positive |
| Plug Type | M |

Environmental

| | |
|-----------------------|---------------------------|
| Operating Temperature | 0C to 40C (32F to 104F) |
| Storage Temperature | -10C to 60C (14F to 140F) |
| Humidity | 0% - 80 % |



Physical Characteristics

| | |
|-------------------|----------------------|
| Color | Black |
| Material | Aluminum and Plastic |
| Product Length | 5.2 in [13.1 cm] |
| Product Width | 3.8 in [97 mm] |
| Product Height | 1.1 in [28 mm] |
| Weight of Product | 16.4 oz [465 g] |

Packaging Information

| | |
|---------------------------|------------------|
| Package Length | 6.1 in [15.6 cm] |
| Package Width | 9.3 in [23.5 cm] |
| Package Height | 2.6 in [65 mm] |
| Shipping (Package) Weight | 34.2 oz [969 g] |

What's in the Box

| | |
|---------------------|---|
| Included in Package | HDMI over IP receiver |
| | foot pad set |
| | universal power adapter (NA / EU / UK / AU) |
| | mounting bracket |
| | instruction manual |

****Product appearance and specifications are subject to change without notice.***

