## Product data sheet Characteristics

# GVSUPS30KB5FS

Galaxy VS UPS 30kW 208V, 3 internal 9Ah smart modular battery strings, expandable to 5, Start-up 5x8



$\sim$			
	)ve	r\/I	٨

OVOIVION	
Description	Highly efficient, easy-to-deploy 30kW, 208V 3-phase UPS that brings best-in-class power protection and low total cost of ownership to edge, small and medium data centers, as well as to critical infrastructure in commercial and industrial applications. Includes 5x8 start-up service and 3 smart modular high capacity battery strings, expandable to 5 strings for extended runtime. See the battery runtime chart for details.
Model Name	Galaxy VS UPS 30kW 208V, 3 internal 9Ah smart modular battery strings, expandable to 5, Start-up 5x8
Includes	Battery modules ship installed , Dust filter , EcoStruxure Ready ((UPS)) , Installation manual in Japanese , Integrated network management , Start-Up Service
Standard Lead Time	Usually Ships within 2 Weeks
Product Distribution	Anguilla , Antigua And Barbuda , Aruba , Bahamas , Barbados , Belize , Bermuda , Brazil , Canada , Colombia , Costa Rica , Cuba , Dominican Republic , Ecuador , El Salvador , Falkland Islands (Malvinas) , Guadeloupe , Guatemala , Guyana , Haiti , Honduras , Jamaica , Mexico , Netherlands Antilles , Nicaragua , Panama , Puerto Rico , Trinidad And Tobago , Turks And Caicos Islands , United States , Venezuela , VIRGIN ISLANDS (UNITED STATES)

### Output

•		
Output Power Capacity	30.0 KW / 30.0 kVA	ğ
Max Configurable Power (Watts)	30.0 KW / 30.0 kVA	9 2
Nominal Output Voltage	208 3PH	+
Output Voltage Distortion	Less than 5%	<u>.v.</u> 50
Output Frequency (sync to mains)	50 Hz , 60 Hz	 Ž
Other Output Voltages	200, 220V	Substitution of the substi
Crest Factor	2.5	<u>.</u> 0
Crest Factor	Double Conversion Online	, c
Waveform Type	Sinewave	
Output Voltage Tolerance	+/-1% after 50ms	. <u>.</u> 
Overload Operation	150% for 1 minute 125% for 10 minutes	. <u>v</u>
Bypass	Built-in Static Bypass	

#### Input

input	
Nominal Input Voltage	208 3PH

Input voltage range for main operations	177 - 239 (208V) V
Other Input Voltages	200 , 220
Maximum Input Current	107 A
Maximum Short Circuit Withstand (Icw)	65.0
Input Total Harmonic Distortion	Less than 3% for full load

### Batteries & Runtime

Battery Type	VRLA
Nominal Battery Voltage	480VDC
End of Discharge Maximum Battery Current	81 A

# Communications & Management

Control panel	Touch Screen LCD User Interface
Audible Alarm	Audible and visible alarms prioritized by severity

### Physical

•	
Maximum Height	1970.0 mm
Maximum Width	550.0 mm
Maximum Depth	847.0 mm
Net Weight	665.0 kg
Shipping Weight	690.0 kg
Shipping Height	2082.0 mm
Shipping Width	755.0 mm
Shipping Depth	1010.0 mm
Color	Gloss level 85%, RAL 9003, White

### Environmental

Operating Environment	0 - 40 °C
Operating Relative Humidity	0 - 95 (non-condensing) %
Operating Elevation	0-990 meters
Storage Temperature	-15 - 40 °C
Storage Relative Humidity	10 - 80 (non-condensing) %
Storage Elevation	0-3 meters
Audible noise at 1 meter from surface of unit	54.000 dB
Online Thermal Dissipation	6526.000 BTU/hr
Protection Class	IP 20

### Conformance

Approvals	CSA C22.2 NO. 107.3 , FCC Part 15 Class A , IEC 62040-1-1 , IEC 62040-2 , IEC 62040-3 , OSHPD , UL 1778 5th edition
Standard warranty	1 year on-site repair or replace with factory authorized Start-Up

### Sustainable Offer Status

RoHS	Compliant
REACH	REACH: Contains SVHCs