

35 ft DisplayPort Cable with Latches - M/M

**Product ID:** DISPLPORT35L



The DISPLPORT35L 35-foot DisplayPort cable provides a connection of up to 35ft between a DisplayPort source and a DisplayPort display, supporting resolutions up to 1920x1200, with no loss of signal quality – more than double the typical DisplayPort connection distance limitation of 16ft.

Its 26 gauge (AWG) pure copper wire, and Aluminum and Mylar shielding helps to eliminate EMI and RFI interference, while its small USB-sized latching connectors support two-way display connectivity and optional audio support.

The DISPLPORT35L DisplayPort cable is both HDCP and DPCP capable, ensuring that digitally protected content is displayed properly on the connected display.

## Certifications, Reports and Compatibility

### Applications

- Connecting a DisplayPort display to a PC or alternative DisplayPort source

### Features

- Molded latching connectors with strain relief
  - Supports the DPCP (DisplayPort Content Protection) standard in addition to HDCP
  - Designed and manufactured to DisplayPort standards
-

## Hardware

Warranty	Lifetime
Number of Conductors	19
Connector Plating	Nickel
Cable Jacket Material	PVC - Polyvinyl Chloride
Cable Shield Material	Aluminum-Mylar Foil with Braid
Fire Rating	CMG Rated (General Purpose)

---

## Connector(s)

Connector A	DisplayPort (20 pin)
Connector B	DisplayPort (20 pin)

---

## Physical Characteristics

Color	Black
Connector Style	Latching
Wire Gauge	26 AWG (0.404 mm)
Cable Length	35.0 ft [10.7 m]
Cable OD	0.3 in [8.5 mm]
Product Length	35.0 ft [10.7 m]
Product Width	0.8 in [20.5 mm]
Product Height	0.4 in [10.8 mm]
Weight of Product	27.5 oz [780.0 g]

---

## Packaging Information

Package Length	13.8 in [35.0 cm]
Package Width	18.1 in [46.0 cm]
Package Height	2.9 in [73.0 mm]
Shipping (Package) Weight	28.0 oz [793.0 g]

---

**What's in the  
Box**

Included in Package      35 ft DisplayPort Cable with Latches - M/M

---

*\*Product appearance and specifications are subject to change without notice.*

