

## 12U Sideways Wall-Mount Rack for Servers

**Product ID:** RK1219SIDEM



The RK1219SIDEM Wall Mount/Side Mount Deep Open Frame Rack/Cabinet (12U, 19in Wide) lets you mount your servers, A/V or network equipment facing perpendicular to the wall for easy access to mounted devices and equipment. The cabinet/rack features open access to both the front and back of your devices, making it easy to adjust cabling, view LEDs and access configuration buttons as needed; plus, the nature of the sidemount configuration allows for deeper mounting depths than typical wallmount racks. This TAA compliant product adheres to the requirements of the US Federal Trade Agreements Act (TAA), allowing government GSA Schedule purchases.

Constructed of high-quality SPCC cold-rolled steel, for strength and durability, the open frame equipment rack allows for maximum airflow while still supporting a maximum weight capacity of 159 kg (350 lbs). The wall mount rack also ships complete with all of the M5 screws and cage nuts required to mount your equipment, saving the expense of purchasing them separately.

Backed by a StarTech.com Lifetime warranty.

### Certifications, Reports and Compatibility

#### Applications

- Perfect for installing network switches out of the way and high up on a wall in a branch office, warehouse, or superstore location
- Ideal for small and medium businesses requiring small rack solutions dispersed throughout the organization
- Mount Audio/Video broadcast or distribution components

#### Features

- Wall mount holes are 16" from center-to-center, for mounting to any standard wooden studs (easily mounts to concrete or steel as well)
- Package includes all necessary screws/nuts for mounting equipment
- TAA compliant for GSA Schedule purchases
- Mounts equipment facing perpendicular to the wall
- Sturdy SPCC cold-rolled steel construction
- Open frame design for optimum airflow
- Ships fully assembled and ready to use

---

#### Hardware

Warranty	Lifetime
Wallmountable	Yes
Rack Type	4-Post
Frame Type	Open Frame
U Height	12U
Special Features	Ships Fully Assembled Wall-Mountable
Mounting Rail Profile	L-Shape
Mounting Hole Types	Square (For Cage Nut)
Industry Standards	EIA/ECA-310-E

---

#### Performance

Weight Capacity	351.4 lb [159 kg]
-----------------	-------------------

---

#### Physical Characteristics

Color	Black
Construction Material	Steel

---

#### Product Measurements

Product Length	22.3 in [56.6 cm]
----------------	-------------------



Product Width	21.2 in [53.8 cm]
Product Height	25.9 in [65.9 cm]
Weight of Product	46.7 lb [21.2 kg]
Maximum Mounting Depth	20.8 in [52.9 cm]

---

**Packaging Information**

Flat Pack (Assembly Required)	No
Package Length	23.3 in [59.2 cm]
Package Width	22.1 in [56.2 cm]
Package Height	27.2 in [69.0 cm]
Shipping (Package) Weight	54.6 lb [24.7 kg]

---

**What's in the Box**

Included in Package	12U Rack
	M5 Screws
	M5 Cage Nuts

---

***\*Product appearance and specifications are subject to change without notice.***

