Product data sheet Characteristics

GVSUPS30KR0B5GS

Highly efficient, easy-to-deploy 30kW, 480V 3-phase UPS that brings best-in-class power protection and low total cost of ownership to edge, small and medium data centers, as well as to critical infrastructure in commercial and industrial applications. This UPS is for up to 5 smart modular high capacity battery strings, but is supplied without batteries, so you can easily customize the battery runtime. Includes 5x8 start-up service and one additional power module for N+1 redundancy.



Overview

· · · · · · · · · · · · · · · · · · ·	
Description	Highly efficient, easy-to-deploy 30kW, 480V 3-phase UPS that brings-best-in-class power protection and low total cost of ownership to edge, smalland medium data centers, as well as to critical infrastructure in commercial and industrial applications. This UPS is for up to 5 smart modular high capacity-battery strings, but is supplied without batteries, so you can easily customize thebattery runtime. Includes 5x8 start-up service and one additional power module-for N+1 redundancy.
Model Name	Galaxy VS UPS 30kW 480V with N+1 power module, for 5 smart modular 9Ah-battery strings, Start-up 5x8
Includes	Dust filter , EcoStruxure Ready ((UPS)) , Installation manual in Japanese , Integrated network management , Start-Up Service
Standard Lead Time	Usually Ships within 2 Weeks
Product Distribution	Anguilla , Antigua And Barbuda , Argentina , Aruba , Bahamas , Barbados , Belize , Bermuda , Bolivia , Brazil , Canada , Cayman Islands , Chile , Colombia , Costa Rica , Cuba , Dominica , Dominican Republic , Ecuador , El Salvador , Falkland Islands (Malvinas) , Grenada , Guadeloupe , Guatemala , Guyana , Haiti , Honduras , Jamaica , Mexico , Netherlands Antilles , Nicaragua , Panama , Paraguay , Peru , Puerto Rico , SAINT KITTS AND NEVIS , SAINT LUCIA , SAINT VINCENT AND THEGRENADINES , Trinidad And Tobago , Turks And Caicos Islands , United States , Uruguay , Venezuela , VIRGIN ISLANDS (UNITED STATES)

Output

Max Configurable Power (Watts)	30.0 KW / 30.0 kVA	
Nominal Output Voltage	480 3PH	
Output Voltage Distortion	Less than 3%	
Output Frequency (sync to mains)	50 Hz , 60 Hz	
Crest Factor	2.5	
	Double Conversion Online	
Waveform Type	Sinewave	

May 19, 2020

Output Voltage Tolerance	+/-1% after 50ms
Output Voltage THD	<1% linear load and <3% non-linear load
Overload Operation	150% for 1 minute 125% for 10 minutes
Bypass	Built-in Static Bypass

Input

Nominal Input Voltage	480 3PH
Input voltage range for main operations	408 - 552 (480) V
Maximum Input Current	45 A
Maximum Short Circuit Withstand (Icw)	65.0
Input Total Harmonic Distortion	Less than 6% for full load

Batteries & amp; Runtime

Battery Type	VRLA
Nominal Battery Voltage	480VDC
End of Discharge Maximum Battery Current	81 A

Communications & Danagement

Control panel	Touch Screen LCD User Interface
Audible Alarm	Audible and visible alarms prioritized by severity

Physical

1970.0 mm
550.0 mm
847.0 mm
250.0 kg
250.0 kg
2082.0 mm
755.0 mm
1010.0 mm
Gloss level 85%, RAL 9003, White

Environmental

Operating Environment	0 - 40 °C
Operating Relative Humidity	0 - 95 (non-condensing) %
Operating Elevation	0-990 meters
Storage Temperature	-15 - 40 °C
Storage Relative Humidity	10 - 80 (non-condensing) %
Storage Elevation	0-3 meters
Audible noise at 1 meter from surface of unit	54.000 dB
Online Thermal Dissipation	3855.000 BTU/hr
Protection Class	IP 20

Conformance

Approvals	CSA C22.2 NO. 107.3 , FCC Part 15 Class A , IEC 62040-1-1 , IEC 62040-2 , IEC 62040-3 , OSHPD , UL 1778 5th edition
Standard warranty	1 year on-site repair or replace with factory authorized Start-Up

Sustainable Offer Status

RoHS	Compliant
REACH	REACH: Contains No SVHCs

