

16 Port 1U Rackmount USB KVM Switch with OSD

Product ID: SV1631DUSBU



The SV1631DUSBU 16 Port 1U Rack Mountable USB KVM Switch with OSD lets you control 16 USB computers from a single console (USB keyboard, USB mouse, VGA monitor).

Convenient push-button and hot-key controls provide quick, reliable switching between connected computers while manual and auto-scan switching modes and an On Screen Display (OSD) offer additional control options.

Designed to ensure maximum space efficiency, the USB KVM switch features a slim 1U design that fits neatly into a server equipment rack/cabinet with the included brackets, and can be cascaded with multiple KVM switches to deliver control of up to 136 computers from this single switch. Rear cable connections help to eliminate cable tangles and minimize workspace disruption.

This product is TAA compliant and backed by a Startech.com 3-year warranty with free lifetime technical support.

The SV1631DUSBU only works with specific 2-in-1 VGA and USB cables (sold separately), a list of StarTech.com approved cables are below:

6 ft Ultra Thin USB VGA 2-in-1 KVM Cable

6 ft Ultra Thin USB VGA 2-in-1 KVM Cable

10 ft Ultra Thin USB VGA 2-in-1 KVM Cable

15 ft Ultra Thin USB VGA 2-in-1 KVM Cable

Certifications, Reports and Compatibility

Applications

- Add single console administration to your Co-location/ISP facility saving you time and money
- Create a scalable, streamlined access solution in your Datacenter or Server Farm
- Perfect for manufacturing line computer control, simplifying access to multiple systems
- Great for PC test/burn-in computer control saving the desk space required for multiple monitors, keyboards and mice
- Ideal for control of multiple PCs in a QA testing environment

Features

- OS Independent – No drivers or software required
- Auto-scan function automatically selects computer sequentially
- Cascade configuration expands system capability
- Front panel push-button and Hotkey switching allow easy computer access
- Identifies and selects computers by the names assigned using the OSD
- USB console connections
- OSD security allows each PC to be password protected
- Plug-and-play system configuration
- Supported Wide Screen Resolutions: 1920x1200, 1920x1080, 1680x1050, 1400x1050, 1440x900, 1360x768
- Supported 4 : 3 Resolutions: 1920x1440, 1600x1200, 1280x1024, 1024x768
- USB Keyboard and Mouse combo supported on one USB connection

Hardware

Warranty	3 Years
Audio	No
KVM Ports	16
PC Interface	USB
PC Video Type	VGA
Number of Monitors Supported	1
Rack-Mountable	Yes

Cables Included No

Daisy-Chain Yes

Performance

On-Screen Display Yes

IP Control No

Hot-Key Selection Yes

Maximum Analog Resolutions 1920x1440 @60Hz (1920x1200 @60Hz - Wide Screen)

Wide Screen Supported Yes

Maximum Number of Users 1

Maximum Cascaded Computers 136

Port Selection Support Push Button, Hotkeys, and OSD (On Screen Display)

MTBF 158000 hours

Connector(s)

Console Interface(s) VGA (15 pin, High Density D-Sub)

USB Type-A (4 pin) USB 2.0

Host Connectors VGA (15 pin, High Density D-Sub)

Software

OS Compatibility OS independent; No software or drivers required

Indicators

LED Indicators Green - Power

Green - PC Online

Red - PC Selected

Power

Power Source AC Adapter Included

Input Voltage 100 - 240 AC



Input Current	0.6A
Output Voltage	12V DC
Output Current	1.5A
Center Tip Polarity	Positive
Plug Type	M
Power Consumption (In Watts)	18

Environmental

Operating Temperature	5°C to 40C (41F to 104F)
Storage Temperature	-20°C to 60C (-4F to 140F)
Humidity	80% RH

Physical Characteristics


Color	Black
Material	Steel
Product Width	21.3 in [54 cm]
Product Height	1.8 in [45 mm]
Product Depth	7.1 in [18 cm]
Weight of Product	6.9 lb [3.1 kg]

Packaging Information

Package Length	18.4 in [46.8 cm]
Package Width	3.5 in [89 mm]
Package Height	10.4 in [26.4 cm]
Shipping (Package) Weight	7.8 lb [3.5 kg]

What's in the Box

Included in Package	16 Port USB KVM Switch
---------------------	------------------------



Mounting Brackets

Bag of Screws

Pack Rubber Feet

Power Adapter

User Manual

****Product appearance and specifications are subject to change without notice.***

