## Product data sheet Characteristics

# GVSUPS40KB5FS

Galaxy VS UPS 40kW 208V, 3 internal 9Ah smart modular battery strings, expandable to 5, Start-up 5x8



#### Overview

Description	Highly efficient, easy-to-deploy 40kW, 208V 3-phase UPS that brings best-in-class power protection and low total cost of ownership to edge, small and medium data centers, as well as to critical infrastructure in commercial and industrial applications. Includes 5x8 start-up service and 3 smart modular high capacity battery strings, expandable to 5 strings for extended runtime. See the battery runtime chart for details.
Model Name	Galaxy VS UPS 40kW 208V, 3 internal 9Ah smart modular battery strings, expandable to 5, Start-up 5x8
Includes	Battery modules ship installed , Dust filter , EcoStruxure Ready ((UPS)) , Installation manual in Japanese , Integrated network management , Start-Up Service
Standard Lead Time	Usually Ships within 2 Weeks
Product Distribution	Anguilla , Antigua And Barbuda , Argentina , Aruba , Bahamas , Barbados , Belize , Bermuda , Bolivia , Brazil , Canada , Cayman Islands , Chile , Colombia , Costa Rica , Cuba , Dominica , Dominican Republic , Ecuador , El Salvador , Falkland Islands (Malvinas) , Grenada , Guadeloupe , Guatemala , Guyana , Haiti , Honduras , Jamaica , Mexico , Netherlands Antilles , Nicaragua , Panama , Paraguay , Peru , Puerto Rico , SAINT KITTS AND NEVIS , SAINT LUCIA , SAINT VINCENT AND THE GRENADINES , Trinidad And Tobago , Turks And Caicos Islands , United States , Uruguay , Venezuela , VIRGIN ISLANDS (UNITED STATES)

### Output

Output Power Capacity	40.0 KW / 40.0 kVA	
Max Configurable Power (Watts)	40.0 KW / 40.0 kVA	<u>w</u> .
Nominal Output Voltage	208 3PH	
Output Voltage Distortion	Less than 5%	
Output Frequency (sync to mains)	50 Hz , 60 Hz	substitute
Other Output Voltages	200, 220V	ი თ დ
Crest Factor	2.5	——————————————————————————————————————
Crest Factor	Double Conversion Online	nirended
Waveform Type	Sinewave	s not
Output Voltage Tolerance	+/-1% after 50ms	tio
Overload Operation	150% for 1 minute 125% for 10 minutes	
Bypass	Built-in Static Bypass	documentation
		Ø

### Input

Nominal Input Voltage	208 3PH
Input voltage range for main operations	177 - 239 (208V) V
Other Input Voltages	200 , 220
Maximum Input Current	143 A
Maximum Short Circuit Withstand (Icw)	65.0
Input Total Harmonic Distortion	Less than 3% for full load

### Batteries & Runtime

Battery Type	VRLA
Nominal Battery Voltage	480VDC
End of Discharge Maximum Battery Current	109 A

### Communications & Management

Control panel	Touch Screen LCD User Interface
Audible Alarm	Audible and visible alarms prioritized by severity

### Physical

,	
Maximum Height	78.0 inches (1970.0 mm)
Maximum Width	22.0 inches (550.0 mm)
Maximum Depth	34.0 inches (847.0 mm)
Net Weight	1500.0 lbs (680.0 kg)
Shipping Weight	1554.0 lbs (705.0 kg)
Shipping Height	82.0 inches (2082.0 mm)
Shipping Width	30.0 inches (755.0 mm)
Shipping Depth	40.0 inches (1010.0 mm)
Color	Gloss level 85%, RAL 9003, White

### Environmental

Operating Environment	32 - 104 °F (0 - 40 °C)
Operating Relative Humidity	0 - 95 (non-condensing) %
Operating Elevation	0-3300ft feet (0-990 meters)
Storage Temperature	5 - 104 °F (-15 - 40 °C)
Storage Relative Humidity	10 - 80 (non-condensing) %
Storage Elevation	0-10 000ft feet (0-3 meters)
Audible noise at 1 meter from surface of unit	57.000 dB
Online Thermal Dissipation	7428.000 BTU/hr
Protection Class	IP 20

### Conformance

Approvals	CSA C22.2 NO. 107.3 , FCC Part 15 Class A , IEC 62040-1-1 , IEC 62040-2 , IEC 62040-3 , OSHPD , UL 1778 5th edition
Standard warranty	1 year on-site repair or replace with factory authorized Start-Up

### Sustainable Offer Status

RoHS	Compliant
REACH	REACH: Contains SVHCs