

# GVSUPS25KR0B5FS

Galaxy VS UPS 25kW 208V with N+1 power module, for 5 smart modular 9Ah battery strings, Start-up 5x8



## Overview

Description	Highly efficient, easy-to-deploy 25kW, 208V 3-phase UPS that brings best-in-class power protection and low total cost of ownership to edge, small and medium data centers, as well as to critical infrastructure in commercial and industrial applications. This UPS is for up to 5 smart modular high capacity battery strings, but is supplied without batteries, so you can easily customize the battery runtime. Includes 5x8 start-up service and one additional power module for N+1 redundancy.
Model Name	Galaxy VS UPS 25kW 208V with N+1 power module, for 5 smart modular 9Ah battery strings, Start-up 5x8
Includes	Dust filter , EcoStruxure Ready ((UPS)) , Installation manual in Japanese , Integrated network management , Start-Up Service
Standard Lead Time	Usually Ships within 2 Weeks
Product Distribution	Anguilla , Antigua And Barbuda , Aruba , Bahamas , Barbados , Belize , Bermuda , Brazil , Canada , Colombia , Costa Rica , Cuba , Dominican Republic , Ecuador , El Salvador , Falkland Islands (Malvinas) , Guadeloupe , Guatemala , Guyana , Haiti , Honduras , Jamaica , Mexico , Netherlands Antilles , Nicaragua , Panama , Puerto Rico , Trinidad And Tobago , Turks And Caicos Islands , United States , Venezuela , VIRGIN ISLANDS (UNITED STATES)

## Output

Output Power Capacity	25.0 KW / 25.0 kVA
Max Configurable Power (Watts)	25.0 KW / 25.0 kVA
Nominal Output Voltage	208 3PH
Output Voltage Distortion	Less than 3%
Output Frequency (sync to mains)	50 Hz , 60 Hz
Other Output Voltages	200, 220V
Crest Factor	2.5
Crest Factor	Double Conversion Online
Waveform Type	Sinewave
Output Voltage Tolerance	+/-1% after 50ms
Output Voltage THD	<1% linear load and <3% non-linear load
Overload Operation	150% for 1 minute 125% for 10 minutes
Bypass	Built-in Static Bypass

## Input

Nominal Input Voltage	208 3PH
-----------------------	---------

Input voltage range for main operations	177 - 239 (208V) V
Other Input Voltages	200 , 220
Maximum Input Current	90 A
Maximum Short Circuit Withstand (Icw)	65.0
Input Total Harmonic Distortion	Less than 6% for full linear load

### Batteries & Runtime

Battery Type	VRLA
Nominal Battery Voltage	480VDC
End of Discharge Maximum Battery Current	68 A

### Communications & Management

Control panel	Touch Screen LCD User Interface
Audible Alarm	Audible and visible alarms prioritized by severity

### Physical

Maximum Height	1970.0 mm
Maximum Width	550.0 mm
Maximum Depth	847.0 mm
Net Weight	250.0 kg
Shipping Weight	250.0 kg
Shipping Height	2082.0 mm
Shipping Width	755.0 mm
Shipping Depth	1010.0 mm
Color	Gloss level 85% , RAL 9003 , White

### Environmental

Operating Environment	0 - 40 °C
Operating Relative Humidity	0 - 95 (non-condensing) %
Operating Elevation	0-990 meters
Storage Temperature	-15 - 40 °C
Storage Relative Humidity	10 - 80 (non-condensing) %
Storage Elevation	0-3 meters
Audible noise at 1 meter from surface of unit	54.000 dB
Online Thermal Dissipation	4049.000 BTU/hr
Protection Class	IP 20

### Conformance

Approvals	CSA C22.2 NO. 107.3 , FCC Part 15 Class A , IEC 62040-1-1 , IEC 62040-2 , IEC 62040-3 , OSHPD , UL 1778 5th edition
Standard warranty	1 year on-site repair or replace with factory authorized Start-Up