

#### 5-Port Industrial Ethernet Switch - DIN Rail Mountable

**Product ID:** IES5102



This compact 5-port industrial Ethernet switch is engineered to deliver fast, reliable network connectivity and durability in the most demanding industrial environments. It provides top performance in a wider range of operating temperatures than conventional network switches, making it ideal for factories and warehouses.

Designed with a rugged IP30-rated housing, the network switch delivers maximum performance even in harsh industrial conditions. Its wide-range terminal block input gives you the flexibility to power the switch as required, based on your own power input source, while its wide operating temperature range keeps your network running smoothly.

This industrial Ethernet switch is easy to install, with an attached metal bracket for DIN rail mounting on equipment racks and cabinets.

Now you can eliminate the hassle of troubleshooting mismatched speed and duplex settings. This switch gives you full/half-duplex auto-negotiation and auto MDI/MDIX operation, enabling you to connect your network devices quickly and easily with little to no configuration required.

With lower overall power consumption, the Ethernet switch enhances your energy efficiency, in turn helping you reduce monthly costs.

The IES5102 is backed by a StarTech.com 2-year warranty and free lifetime technical support.

### Certifications, Reports and Compatibility

### **Applications**

- · Well suited for networks in demanding industrial applications such as warehouses and factories
- A great way to enhance network connectivity, adding small workgroups to an existing network



• Install in a server rack or cabinet in a network room or test lab environment

#### **Features**

- Network up to 5 Ethernet devices, even in industrial settings, with a robust IP30-rated switch
- Wide-range 12-48V DC terminal block input
- Easy installation with an integrated DIN rail bracket
- Wider range of operating temperatures, ideal for industrial environments
- IEEE 802.3az Energy-Efficient Ethernet
- Supports 10BaseT/100BaseTX and Full-Duplex/Half-Duplex Auto-negotiation
- Supports IEEE 802.3x flow control and back pressure
- Store-and-forward switching mechanism

	wa	

Warranty 2 Years

Ports 5

Interface RJ45 (10/100 Ethernet)

Regulatory Approvals EN61000-6-2<br/>br/>EN61000-6-4<br/>br/>EN61000-4-3 (Radiated RFI

Standards) <br/>
<br/>
EN61000-4-4 (Burst Standards) <br/>
EN61000-4-6 (Induced RFI Standards) <br/>
<br/>
EN61000-4-8 (Magnetic Field

Standards)<br/>lEC60068-2-6 Fc (Vibration)<br/>lEC60068-2-27 Ea

(Shock)<br/>

Industry Standards IEEE 802.3 (10BASE-T), IEEE 802.3u (100BASE-TX)

IEEE 802.3az (Energy-Efficient Ethernet)

IEEE 802.1P Quality of Service (QoS)

#### **Performance**

Maximum Data Transfer

200 Mbps (Full-Duplex)

Rate

Maximum Cable Length 328.0 ft [100 m]

Buffer Size 56 KB

Flow Control IEEE 802.3x Full-Duplex



Surge Protection ESD: EN61000-4-2 <br/>br/>Surge: EN61000-4-5

Compatible Networks 10/100 Mbps

Auto MDIX Yes

Full Duplex Support Yes

Jumbo Frame Support No

Switching Architecture Store-and-Forward

MTBF 1,179,133 Hours

Connector(s)

External Ports RJ-45

Terminal Block (3 Wire)

Software

OS Compatibility OS Independent; No additional drivers or software required

**Indicators** 

LED Indicators Power

Link/Activity

Activity (100 Mbps)

**Power** 

Power Source Terminal Block

Input Voltage 12 ~ 48 DC

Power Consumption (In

Watts)

2.12W Max

**Environmental** 

Operating Temperature -10C to 60C (14F to 140F)

Storage Temperature -25C to 85C (-13F to 185F)

Humidity 5~95% RH (Non-Condensing)

Physical Characteristics



Color	Black

Material Plastic

Product Length 2.8 in [70 mm]

Product Width 1.0 in [25 mm]

Product Height 4.3 in [11 cm]

Weight of Product 5.3 oz [150 g]

# Packaging Information

Package Length 7.8 in [19.8 cm]

Package Width 7.0 in [17.8 cm]

Package Height 3.1 in [79 mm]

Shipping (Package)

Weight

11.0 oz [312 g]

## What's in the Box

Included in Package

5 Port Ethernet Switch (w/ Attached DIN Rail Bracket)

**Terminal Block** 

Instruction Manual CD

<sup>\*</sup>Product appearance and specifications are subject to change without notice.