

## 6in DVI-D Dual Link Digital Port Saver Extension Cable M/F

#### **Product ID: DVIDEXTAA6IN**



The DVIDEXTAA6IN 6-inch DVI-D Port Saver Cable/coupler avoids expensive repairs to a computer or display. It does this by extending the port by 6in, thereby eliminating the weight and stress that would typically be placed on the port by a DVI cable. This is especially useful in an environment where cables are unplugged and re-inserted frequently.

The 6in DVI-D cable supports resolutions of up to 2560x1600 and transmission rates of up to 9.9 Gbits/sec, and is fully compliant with DVI DDWG standards.

Designed and constructed for maximum durability, this high quality video cable is backed by StarTech.com's Lifetime Warranty.

# Certifications, Reports and Compatibility

## **Applications**

• Extend a video card or monitor DVI-D port by 6in, to protect against damage from frequent connect/disconnects

### **Features**

- Supports a maximum resolution of 2560x1600
- High-speed digital transmission rate of up to 9.9 Gbits/sec
- · Aluminum-Mylar Foil with Braided Shielding
- Supports hot-plugging of DVI display devices



### • Compliant with DVI DDWG Standards

Hardware

Warranty Lifetime

Connector Plating Nickel

Cable Jacket Material PVC - Polyvinyl Chloride

Cable Shield Material Aluminum-Mylar Foil with Braid

Connector(s)

Connector A DVI-D (25 pin)

Connector B DVI-D (25 pin)

Physical Characteristics

Color Black

Wire Gauge 28 AWG

Cable Length 6.0 in [15.2 cm]

Product Length 6.0 in [15.2 cm]

Product Width 1.6 in [40 mm]

Product Height 0.6 in [16 mm]

Weight of Product 2.8 oz [79 g]

Packaging Information

Package Quantity 1

Package Length 8.9 in [22.5 cm]

Package Width 4.9 in [12.5 cm]

Package Height 0.6 in [16 mm]

Shipping (Package) 3.0 oz [84 g]

Weight

What's in the Box

Included in Package 6in DVI-D Dual Link Digital Port Saver Cable M/F



\*Product appearance and specifications are subject to change without notice.