


400G Duplex Singlemode 8.3/125 OS2 Fiber Optic Cable (CS-UPC/LC-UPC), Round LSZH Jacket, Yellow, 5 m

MODEL NUMBER: N381L-05M



400 GbE Ethernet cable supports high bandwidths necessary for next-generation cloud services, hyperscale data centers and telecom carriers.

Features

400 GbE Cable Supports Higher Bandwidths Needed for Next-Gen Data Networking

As the amount of traffic in data networks grows, so does the need for next-generation devices and fiber cables to support much higher bandwidths in cloud services, hyperscale data centers, telecom applications and equipment OEM companies. This duplex singlemode 8.3/125 OS2 cable is an ideal choice for 400G Ethernet applications up to two kilometers (at 1310 nm). It is also backward compatible with 40 Gb and 100 Gb networks, so you can future-proof your current application for an eventual upgrade to 400 Gb.

Compact CS Connector Designed for the Latest QSFP-DD Transceivers

The CS end is 40 percent smaller than a standard LC connector, making it compatible with the latest 400G QSFP-DD transceivers and an excellent solution for high-density network applications. A push/pull tab allows dense vertical stacking in switches or patch panels where space is at a premium and makes the cable easy to install or remove with one hand.

Yellow Jacket Helps Avoid Misidentification That Can Cause Costly Downtime

The OS2-rated cable has a yellow jacket, which is easy to identify quickly in a crowded patch panel or switch and helps prevent the cable from becoming accidentally disconnected. The round low-smoke zero-halogen (LSZH) jacket limits the amount of toxic smoke emitted in case of combustion, making it suitable for poorly ventilated areas. It also complies with G657A2 bend-insensitive fiber standards, which allows for easy installation without excessive care when storing the fiber due to the increased bend radius.

Highlights

- OS2-rated cable recommended for 400 Gb speeds up to 2 km (@ 1310 nm)
- CS connector 40% more dense than standard LC end for easier cable management
- Smaller-format CS end designed for next-generation 400G QSFP-DD transceivers
- Backward compatible with 40/100 GbE networks to facilitate future-proofing
- Yellow LSZH jacket allows fast, easy identification in a crowded switch or patch panel

Applications

- Connects 400G fiber Ethernet networks in your cloud service, hyperscale data center or telecom application

Package Includes

- N381L-05M 400Gb Duplex Singlemode 8.3/125 OS2 Fiber Optic Cable, Yellow, 5 m

Specifications

| OVERVIEW | |
|----------------------|--------------|
| UPC Code | 037332258038 |
| Attenuation @ 1310NM | 0.35dB/KM |
| Clad Diameter | 125 micron |



| | |
|--------------------------------------|-------------------------------|
| Core Diameter | 8.3 micron |
| Number of Fibers | 2 |
| Primary Coating Diameter | 600 |
| Technology | Singlemode |
| Optical Mode | OS2 |
| Attenuation @ 1550NM | 0.21dB/KM |
| INPUT | |
| Cable Length (ft.) | 16.4 |
| Cable Length (m) | 5 |
| Cable Length (in.) | 196.9 |
| ISOLATION | |
| Insertion Loss | <0.30dB |
| PHYSICAL | |
| Cable Jacket Rating | LSZH |
| Cable Jacket Type | LSZH |
| Color | Blue; Yellow |
| Minimum Bend Radius | 20MM (DYNAMIC); 10MM (STATIC) |
| ENVIRONMENTAL | |
| Operating Temperature Range | -4 to 140 F (-20 to 60 C) |
| Storage Temperature Range | -4 to 140 F (-20 to 60 C) |
| Operating Humidity Range | 5% TO 85% RH, NON-CONDENSING |
| Storage Humidity Range | 5% TO 85% RH, NON-CONDENSING |
| COMMUNICATIONS | |
| Network Speed | 400Gbe |
| CONNECTIONS | |
| Side A - Connector 1 | CS (MALE) |
| Side B - Connector 1 | LC DUPLEX (MALE) |
| FEATURES & SPECIFICATIONS | |
| Transmission Distance | 2KM @ 1310NM WAVELENGTH |
| SPECIAL FEATURES | |



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

| | |
|-------------------------------------|---------------------------|
| Push/Pull Tabs | Yes |
| STANDARDS & COMPLIANCE | |
| Approvals | RoHS, REACH |
| WARRANTY | |
| Product Warranty Period (Worldwide) | Lifetime limited warranty |

© 2020 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>