

## Heavy Duty 2-Post Rack - 16U

**Product ID:** 2POSTRACK16



StarTech.com

This 2-post rack stands on your floor or desktop to provide 16U of storage space for EIA-310-D compliant 19" rack-mount devices, such as telecommunication and A/V equipment. The rack creates a robust storage solution, with support for a total load capacity of 160 kg (350 lb.).

This compact 2-post mounting solution offers a small footprint, and it's engineered to provide exceptional stability, with a total weight capacity of up to 160 kg (350 lb.). The rack fits in virtually any environment, and can be positioned on any surface, such as your floor, desk or table.

The 2-post server rack comes in a flat-packed box to reduce shipping volume, which also significantly reduces your costs in shipping. The rack is packaged efficiently, so you can easily store it for deployment at a later date.

To help make your equipment install easier, this rack includes tool-less clip nuts that seamlessly work with the punched round holes featured on this rack. The tool-less clip nuts provide an easy-to-install nut, unlike square cage nuts which can be a hassle.

The 2POSTRACK16 is backed by a lifetime StarTech.com warranty with free technical support.

## Certifications, Reports and Compatibility

### Applications

- Use this cabinet to house your A/V equipment in a restaurant or bar, where space may be limited
- Rack-mount the equipment in your repair center or technology shop
- House equipment in audio-video editing rooms, or radio and television broadcast studios

## Features

- Save space with a compact 2-post rack solution
- Get heavy-duty weight capacity up to 350 lb. (158 kg)
- Reduce your shipping costs with a flat-packed rack
- Easy equipment installation with tool-less clip nuts
- Maximize compatibility with EIA-310-D compliance
- 16U of rack space

---

### Hardware

Warranty	Lifetime
Wallmountable	No
Rack Type	2-Post
Frame Type	Open Frame
U Height	16U
Special Features	Easy Assembly
Mounting Hole Types	Circle (For Clip Nut)
Industry Standards	EIA/ECA-310-E

---

### Physical Characteristics

Color	Black
Construction Material	Steel

---

### Product Measurements

Product Length	12.0 in [30.5 cm]
Product Width	20.4 in [51.8 cm]
Product Height	31.0 in [78.7 cm]
Weight of Product	17.7 lb [8.0 kg]

---

### Packaging Information



Flat Pack (Assembly Required)	Yes
Package Length	35.7 in [90.7 cm]
Package Width	13.7 in [34.8 cm]
Package Height	2.9 in [73 mm]
Shipping (Package) Weight	20.5 lb [9.3 kg]

---

**What's in the Box**

Included in Package	Right Bracket
	Left Bracket
	Top Bracket
	Bottom Bracket
	Rubber Feet
	10-32 Phillips Screws
	10-32 Mounting Screws
	Clip Nuts
	User Manual

---

***\*Product appearance and specifications are subject to change without notice.***

