

1-port PCI Express RS232 Serial Adapter Card - PCIe RS232 Serial Host Controller Card - PCIe to Serial DB9 - 16950 UART - Low Profile Expansion Card - Windows & Linux

Product ID: PEX1S953LP



This RS232 Serial Adapter Card lets you add an RS232 DB9 serial port to your computer through a PCI Express (PCIe) slot. It enables you to interact with serial devices such as card readers, printers, PIN pads, and modems, at speeds of up-to 921.4Kbps.

With broad OS support, including for Windows and Linux, this PCI Express card is easy to integrate into mixed environments. The card comes pre-configured with a low-profile bracket, and includes an optional full-profile bracket, so installation is easy regardless of the case form factor.

This PCIe to serial adapter supports the following features:

- Compatible with industry standard 16950 UART
- Supports max baud rate of up-to 921.4Kbps
- Provides 5/12V power output on Pin 9 when external power is connected
- 128-byte depth FIFO per transmitter and receiver
- Supports 9, 8, 7, 6, 5 data bits
- Asix AX99100 chipset
- PCI Express 1.1 compliant

PEX1S953LP is backed by a StarTech.com lifetime warranty and free lifetime technical support.

## **Certifications, Reports and Compatibility**



## **Applications**

- Install in home or office workstations
- Connect in retail POS applications
- Connect to automated self-service kiosks or ATM machines
- Interact with RS232 serial devices like card readers or printers

## **Features**

- 1 PORT SERIAL CARD: Serial controller card w/ 16950 UART based on ASIX AX99100, allows 1x DB9 port w/bi-directional RS232 speeds up to 921.6Kbps per port, available 256 byte FIFO buffer & 9th data bit; Upgraded version of our popular card PEX1S952LP
- OPTIONAL CONFIGURABLE POWER: PCI Express RS232 serial adapter card provides choice of 12v, 5v, or none through pin 9 w/up to 2A total
- STANDARD PROFILE & LOW PROFILE BRACKET: PCIe serial card comes w/ a low profile bracket pre-installed & 1x full profile bracket is incl for versatile install; Supports Windows & Linux
- VERSATILE APPLICATIONS: For low/standard profile desktop/servers w/ uses in point of sale terminals, PLCs, control/automation in factories, scientific sensors, medical equipment, scanner, oscilloscope
- THE IT PRO'S CHOICE: Designed and built for IT Professionals, this PCIe serial adapter card is backed for life, including free lifetime 24/5 multi-lingual technical assistance

Hardware		
	Warranty	Lifetime
	Ports	2
	Interface	Serial
	Bus Type	mini PCI Express
	Card Type	Low Profile (SP bracket incl.)
	Port Style	Integrated on Card
	Chipset ID	Asix AX99100
Performance		
	Serial Protocol	RS-232
	Max Baud Rate	921.6 Kbps



Data Bits 5, 6, 7, 8, 9

FIFO 256 Bytes

Flow Control None, Xon/Xoff, RTS/CTS

Parity None, Odd, Even, Space, Mark

Stop Bits 1, 1.5, 2

MTBF 277,385 hours

Connector(s)

Connector Type(s) PCI Express x1

Internal Ports LP4 (4 pin; Large Drive Power)

External Ports DB-9 (9 pin, D-Sub)

**Software** 

OS Compatibility Windows 7, 8, 8.1, 10, 11

Windows Server 2003, 2008 R2, 2012, 2012 R2, 2016

Linux 2.4.x to 2.6.x <i>LTS Versions only</i>

Microsoft WHQL Certified Yes

Special Notes / Requirements

Note Selectable power output on pin 9 of the serial port

**Environmental** 

Operating Temperature 0C to 70C (32F to 158F)

Storage Temperature -20C to 80C (-4F to 176F)

Humidity 20~80% RH

Physical Characteristics

Color Green

Material Steel

Product Length 3.9 in [98.0 mm]

Product Width 2.6 in [67.0 mm]



	Product Height	5.9 in [15.0 cm]
	Weight of Product	1.6 oz [44.0 g]
Packaging Information		
	Package Length	6.7 in [17.0 cm]
	Package Width	5.6 in [14.2 cm]
	Package Height	1.2 in [30.0 mm]
	Shipping (Package) Weight	4.0 oz [112.0 g]
What's in the Box		·
	Included in Package	PCIe Serial Card
		Full-Profile Bracket
		User Manual

<sup>\*</sup>Product appearance and specifications are subject to change without notice.