

5 Port Unmanaged Industrial Gigabit Ethernet Switch - DIN Rail / Wall-Mountable

Product ID: IES51000



The IES51000 5-Port Industrial Ethernet Switch offers 5 Gigabit Ethernet ports in a compact, IP30-rated metal enclosure, making it the ideal network solution for harsh industrial environments such as factory floors, warehouses or large junction boxes.

Quickly connect your network devices with little to no configuration. This unmanaged industrial network switch supports 10/100/1000 Mbps transfer speeds, full/half-duplex auto-negotiation, jumbo frames and auto MDI/MDIX, which helps to eliminate the hassle of troubleshooting mis-matched speed and duplex settings.

Providing seamless operation in the event of power dips or failures, the switch features redundant 12-58V DC terminal block power inputs to help prevent unnecessary downtime. When used with two power sources, the switch also supports alarm relay contacts that you can wire to your existing alarm circuit to notify you instantly when a power disruption occurs.

For easy installation and dependable performance in harsh environments, the switch can be DIN Rail or wall mounted and features a compact, IP30-rated enclosure with an extended operating temperature range (-40C to 75C).

Backed by a StarTech.com 2-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility

Applications

- Ideal for industrial applications such as warehouses and junction boxes without temperature control
- Suitable for adding Gigabit Ethernet on factory / manufacturing floors
- Great for adding small workgroups to an existing network

Features

- 5 10/100/1000 Mbps unmanaged RJ45 Ethernet ports
- IP30-rated DIN rail and wall-mountable metal enclosure
- Wide-range redundant power via two 12-58V DC terminal block inputs, with alarm relay
- Overcurrent and reverse polarity protection
- Extended operating temperature range (-40C to 75C)
- Speed / duplex auto-negotiation and auto-MDIX detection on each port
- Up to 9K jumbo frame support
- IEEE 802.3az Energy-Efficient Ethernet
- Supports IEEE 802.3x flow control and back-pressure

Hardware

Warranty	2 Years
Ports	5
Interface	RJ45 (Gigabit Ethernet)
Industry Standards	IEEE 802.3 10BASE-T, IEEE 802.3u 100BASE-TX, IEEE 802.3ab 1000BASE-TX
	IEEE 802.1p QoS, IEEE 802.3az Energy-Efficient Ethernet, IEEE 802.3ad Link Aggregation
	IP30 (Enclosure)

Performance

Maximum Data Transfer Rate	2 Gbps (Full-Duplex)
Maximum Cable Length	328.0 ft [100 m]
Buffer Size	128 KB
Flow Control	Half-duplex back-pressure and IEEE802.3x full-duplex
Compatible Networks	10/100/1000 Mbps
Auto MDIX	Yes



Full Duplex Support	Yes
Jumbo Frame Support	9K max.
Switching Architecture	Store-and-Forward

Connector(s)

Connector Type(s)	RJ-45 Terminal Block (6 Wire)
-------------------	----------------------------------

Software

OS Compatibility	OS Independent; No additional drivers or software required
------------------	--

Indicators

LED Indicators	P1 (Power) indicator P2 (Power) indicator ALM (Alarm) indicator Link / Act Speed indicator
----------------	--

Power

Power Source	Terminal Block
Input Voltage	12 ~ 58 DC
Power Consumption (In Watts)	3.63W Max.

Environmental

Operating Temperature	-40C to 75C (-40F to 167F)
Storage Temperature	-40C to 85C (-40F to 185F)
Humidity	5~95% RH (Non-Condensing)

Physical Characteristics

Color	Black
Material	Steel
Product Length	4.4 in [11.1 cm]



Product Width	3.5 in [89.0 mm]
Product Height	1.1 in [28.0 mm]
Weight of Product	11.6 oz [328.0 g]

Packaging Information

Package Length	6.9 in [17.6 cm]
Package Width	5.5 in [13.9 cm]
Package Height	3.3 in [83.0 mm]
Shipping (Package) Weight	18.5 oz [523.0 g]

What's in the Box

Included in Package	Industrial Ethernet Switch
	Wall-Mount Brackets
	DIN-Rail Clip
	Screws
	Terminal Block
	Instruction Manual

****Product appearance and specifications are subject to change without notice.***

