

25U Server Rack Cabinet - 4 Post Adjustable Depth 7-35" Locking Vented Mobile/Rolling Network/Data/IT Equipment Enclosure w/Casters/Hook & Loop Dell PowerEdge HP ProLiant

Product ID: RK2537BKM



This 25U server rack provides a sleek, secure cabinet for storing standard 19" rack-mount devices such as Dell, HP, and IBM servers, along with telecommunication and A/V equipment. The rack is compatible with EIA-310 compliant equipment and supports a total load capacity of 1500 kg (3307lb.).

This rack offers a variety of features that make it easy to install your equipment. With adjustable mounting rails, you can easily change the rail depth from 7 to 35in. (76.2 mm - 939.8 mm) to support full-depth equipment. The added depth also provides support for additional cable and power management behind your equipment.

The rack features grommet holes on the ceiling and floor panels, which make it easy to run cabling in and out of the cabinet for discreet cable management. The rack also features grounding lugs that enable you to ground your equipment for added protection, and tool-less accessory mounting rails so you can mount 0U vertical cable managers and PDUs.

For hassle-free cable management, the rack includes a 3-meter roll of hook-and-loop cable tie that makes it easy to keep your cables tidy. You can cut the self-gripping fabric to any size, and bind your equipment cables together or to the rack.

To provide hassle-free deployment the rack ships fully assembled.

To keep your rack-mounted equipment secure, this rack features front and rear locking mesh doors that also increase airflow to provide passive cooling.

The rack also has a removable side panel with an independent quick-release lock that enables you to access your equipment easily, while still keeping it secure. Plus, a quick-release ceiling panel you can remove without interfering with cable runs that are running through your rack.

The cabinet features casters, providing ease of mobility around your office, studio or server room. Plus, the width and height of the rack fit through standard doorways, giving you the freedom to wheel your server rack into different rooms as needed.

The RK2537BKM is backed by a StarTech.com 5-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility



Applications

- Deploy in technology shops and repair centers that have limited space but tend to have mountable equipment that requires security
- Install rack-mount servers, KVM switches, networking equipment and cabinet consoles
- House rack-mount audio/video equipment for broadcasting in your editing room or television studio

Features

- HALF HEIGHT SECURE RACK: 4 Post 25U 19" Server rack cabinet w/adjustable depths of up to 35", internal depth 42.3", dual panel doors for added accessibility; Locking doors & sides w/keys included
- FULLY ASSEMBLED WITH CASTERS: Heavy duty pre-built w/casters & levelling feet to offer maneuverability & stability; Cage nuts/screws & hook & loop tape provided so that equipment can easily be mounted
- DESIGN AND VENTILATION: Rolling mobile data cabinet w/strong mesh doors & vented top allow for abundant airflow & top is also removeable to run cables; 1U intervals are marked for easy identification
- COMPATABILITY: EIA/ECA-310-E Compliant for server/networking equipment, incl. brands like HPE ProLiant, Dell PowerEdge, and Lenovo ThinkSystem; Split rear doors reduce rear access space requirements
- SPECS: 5 year warranty 25U 19in free standing cabinet enclosure Mounting depth 7 to 35in. 3,315lb/1,500kg stationary capacity M6 cage nuts/screws 10ft/3m hook and loop tape Grounding lugs
- Adjustable mounting rails
- 100 x M6 screws and cage nuts included

Hardware	Warranty	2 Years
	Wallmountable	No
	Rack Type	4-Post
	Frame Type	Enclosed Cabinet
	U Height	25U
	Special Features	Adjustable Mounting Rails
	Special Features	Built-in Baying Tabs
	Special Features	Built-in Cable Management
	Special Features	Grounding Lug(s)
	Special Features	Leveling Feet
	Special Features	U-Markings
	Special Features	Ships Fully Assembled

Special Features	Casters (Included)
Mounting Rail Profile	G-Shape
Mounting Hole Types	Square (For Cage Nut)
Industry Standards	EIA/ECA-310-E

Performance	Weight Capacity (Stationary)	3315.0 lb [1500 kg]
--------------------	------------------------------	---------------------

Physical Characteristics	Color	Black
	Front Door Construction	Steel Mesh
	Front Door Features	Secure Key Lock with Removable Front Door
	Side Panel Construction	Steel
	Side Panel Features	Secure Key Lock with Removable Side Panels
	Rear Door Construction	Steel Mesh
	Rear Door Features	Secure Key Lock with Reversible and Removable Back Door

Product Measurements	Internal Width	23.7 in [6.0 cm]
	Internal Depth	3.5 ft [1.1 m]
	Product Length	3.5 ft [1.1 m]
	Product Width	23.8 in [6.0 cm]
	Product Height	3.9 ft [1.2 m]
	Weight of Product	180.8 lb [81.8 kg]
	Maximum Mounting Depth	35.2 in [8.9 cm]
	Minimum Mounting Depth	7.1 in [1.8 cm]
	Product Height with Casters	4.1 ft [1.2 m]

Packaging Information	Flat Pack (Assembly Required)	No
	Package Length	3.8 ft [1.2 m]
	Package Width	26.8 in [6.8 cm]
	Package Height	4.8 ft [1.4 m]
	Shipping (Package) Weight	252.6 lb [114.3 kg]

What's in the Box	Included in Package	Server Rack Cabinet
	Included in Package	M6 Cage Nuts
	Included in Package	M6 Screws
	Included in Package	Plastic Cup Washers
	Included in Package	Keys
	Included in Package	Hey Key
	Included in Package	10 ft. [3 m] Hook and Loop Tape
	Included in Package	User Manual

****Product appearance and specifications are subject to change without notice.***

